

Differential Probe PT-5108



Characteristic

- 2% accuracy.
- Adaptor power supply.
- Standard BNC interface, compatible with any brand's oscilloscope.

Model	PT-5108
Bandwidth(-3dB)	DC-150MHz
Attenuation Ratio	20X, 200X
Accuracy	±2%
Input differential Vp-p	20X:80V; 200X:800V;
Input differential V AC RMS	280V
Input differential V DC	20X:40V; 200X:400V
Common mode voltage RMS	283V
Rise Time	≥2.3ns
Input Impedance	10MΩ//10pF(Single-ended to ground); 20MΩ//5pF(Between the two ends)
Noise RMS	≤1mV
CMRR(Tyical)	60Hz:>80dB; 100Hz:>60dB; 1MHz:>50dB
Oscilloscope input impedance	50Ω
Power adaptor	5V DC
Temperature	0~50°C
Humidity	10~85% RH
Weight	450g
Dimension(L*W*H)	220x85x30mm

● ACCESSORIES



5V Adapter



BP-250



BP-266N



BP-276N



BP-356N

GUANGZHOU PINTECH CO., LIMITED

Web:www.pintech.com.cn

Tel:86-020-82510899

E-mail:sales@pintech.com.cn

Main Products

Optical Isolated Voltage Probe, Differential probe, Oscilloscope probe, High voltage probe, High frequency current probe, Current probe, Digital high voltage meter, High voltage amplifier, Power amplifier, ESD generator, Function generator, Oscilloscope, Spectrum analyzer, multimeter, High voltage power supply, AC power supply, DC power supply and Power equipment instrument.