

OSCILLOSCOPE PROBE CP3101R



Characteristic

- The oscilloscope probe CP series is the most widely used oscilloscope probe. At the same time, it is the most durable and economical probe. There are no active components such as transistors or amplifiers in passive probes, so there is no need to power the probe.

Model	CP3101R
Feature	Readout
Attenuation Ratio	10X
Accuracy	±1%
Bandwidth	DC-100MHz
Rise time	3.5ns
Input impedance	10MΩ
Input capacitance	13pF
Working voltage	600V
Working Temperature	0~50℃
Cable length	1.2m
Weight	90g

● ACCESSORIES



Insulated Tip



Measuring Tip



Spring Hook



Adjustment Tool



Integrated
Circuit Frontier



The Probe Tip
Is Grounded



Channel Identifier

GUANGZHOU PINTECH CO.,LIMITED

Web:www.pintech.com.cn

Tel:86-20-82510899

E-mail:sales@pintech.com.cn

Main Products

Optical Isolated Voltage Probe, Differential probe, Oscilloscope probe, High voltage probe, High frequency current probe, Current probe, Digital high voltage meter, High voltage amplifier, Power amplifier, ESD generator, Function generator, Oscilloscope, Spectrum analyzer, multimeter, High voltage power supply, AC power supply, DC power supply and Power equipment instrument.