

Differential Probe PT-8101



Characteristic

- 2% accuracy.
- Adaptor power supply.
- Standard BNC interface, compatible with any brand's oscilloscope.

Model	PT-8101
Bandwidth(-3dB)	10X:DC-50MHz; 100X:DC-100MHz
Attenuation Ratio	10X, 100X
Accuracy	±2%
Input differential Vp-p	10X:70V; 100X:700V
Input differential V AC RMS	245V
Input differential V DC	10X:35V; 100X:350V
Common mode voltage RMS	245V
Rise Time	≥3.5ns
Impedance	2MΩ//1.18pF(Single-ended to ground); 4MΩ//0.59pF(Between the two ends)
Output	7V
RMS Noise	10X:<10mV; 100X:<50mV
Oscilloscope input impedance	1MΩ
CMRR (typical)	60Hz>80dB; 100kHz>50dB
Options	6V DC/300mA mains adaptor
Length of BNC Cable	90cm
Length of Input Leads	30cm
Temperature	0~50°C
Humidity	20~75%RH
Weight	415g
Dimension(LxWxH)	187x83x41mm

● ACCESSORIES



Adapter



BP-368N

GUANGZHOU PINTECH CO.,LTD

Web:www.pintech.com.cn

Tel:020-82510899

E-mail:sales@pintech.com.cn

Main Products

Optical Isolated Voltage Probe, Differential probe, Oscilloscope probe, High voltage probe, High frequency current probe, Current probe, Digital high voltage meter, High voltage amplifier, Power amplifier, ESD generator, Function generator, Oscilloscope, Spectrum analyzer, multimeter, High voltage power supply, AC power supply, DC power supply and Power equipment instrument.