

OSCILLOSCOPE PROBE CP3308R



Characteristic

- The oscilloscope probe CP series is the most widely used oscilloscope probe. At the same time, it is the most durable and economical probe. There are no active components such as transistors or amplifiers in passive probes, so there is no need to power the probe.

Model	CP3308R
Attenuation Ratio	100X
Accuracy	±1%
Bandwidth	DC-300MHz
Rise time	1.16ns
Input impedance	100MΩ
Input capacitance	5.5pF
Working voltage	2000V
Working Temperature	0~50°C
Cable length	1.35m
Weight	93g

● ACCESSORIES









Insulated Tip

Measuring Tip

Spring Hook

Adjustment Tool

Integrated Circuit Frontier

PL-15

Channel Identifier

GUANGZHOU PINTECH CO.,LIMITED

Web:www.pintech.com.cn
Tel:86-20-82510899
E-mail:sales@pintech.com.cn

Main Products

Optical Isolated Voltage Probe, Differential probe, Oscilloscope probe, High voltage probe, High frequency current probe, Current probe, Digital high voltage meter, High voltage amplifier, Power amplifier, ESD generator, Function generator, Oscilloscope, Spectrum analyzer, multimeter, High voltage power supply, AC power supply, DC power supply and Power equipment instrument.