





RoHS




Circuit Diagram




PCB Layout(Pattern Side)



短柄贴膜
Short handle film



凸柄
Convex handle



短柄
Short handle

NOTE:

- 1.Rating: 24V 25mA DC
- 2.Insulation Resistance: $\geq 100 \text{ M}\Omega$
- 3.Withstand voltage: AC 500V 1Minute
- 4.Operating Force Range: 1000gf Max
- 5.Mechanical Life: 3,000 Cycles

⑥	Terminal		6	Brass	Gold plating
⑦	Shrapnel		3	Beryllium copper	Gold plating
⑧	Handle		3	PA46	White
⑨	Cover		1	PPS	Black
⑩	Base		1	PPS	Black
NO.	Name	Number	Qty	Materil	Remarks

Number of digits(位数)		1P	2P	3P	4P	5P	6P	7P	8P	9P	10P	12P
Cover/black 盖子/黑色	凸柄 Convex handle	DSIC-01LS	DSIC-02LS	DSIC-03LS	DSIC-04LS	DSIC-05LS	DSIC-06LS	DSIC-07LS	DSIC-08LS	DSIC-09LS	DSIC-10LS	DSIC-12LS
	短柄 Short handle	DSIC-01LD	DSIC-02LD	DSIC-03LD	DSIC-04LD	DSIC-05LD	DSIC-06LD	DSIC-07LD	DSIC-08LD	DSIC-09LD	DSIC-10LD	DSIC-12LD
	短柄贴膜 Short handle film	DSIC-01LF	DSIC-02LF	DSIC-03LF	DSIC-04LF	DSIC-05LF	DSIC-06LF	DSIC-07LF	DSIC-08LF	DSIC-09LF	DSIC-10LF	DSIC-12LF

							angle	±2'		design		date		name	DIP SWITCH
							10~30	±0.30		Review		date			
							5~10	±0.20		Approved		date			
							~ 5	±0.10		Drawing number:			model		
					modifv	Review	Approved	Tolerance not specified	Proportion	1:1	unit	mm	gape number		A4 