



1SS355

Plastic-encapsulate diodes

Product data sheet

1. General description

Fast switching diode encapsulated in a small SOD-323 Surface-Mounted Device (SMD) plastic package.



2. Features

- Fast Switching Speed
- Surface Mount Package Ideally Suited for Automatic Insertion
- For General Purpose Switching Applications
- High Conductance

3. Applications

- Surface Mount Package Ideally Suited for Automatic Insertion
- For General Purpose Switching Applications

4. Quick reference data

Table 1. Quick reference data

Parameter	Symbol	Limit	Unit
Non-Repetitive Peak Reverse Voltage	V_{RM}	90	V
RMS Reverse Voltage	$V_{R(RMS)}$	80	V
Forward Continuous Current	I_{FM}	225	mA
Average Rectified Output Current	I_O	100	mA
Non-Repetitive Peak Forward Surge Current @ $t=8.3ms$	I_{FSM}	2.0	A
Power Dissipation	P_d	200	mW

5. Pinning information

Table 2. Pinning information

Pin	Name	Description	Simplified outline	Graphic symbol
1	Cathode	connect to IO		
2	Anode	connect to IO		

6. Ordering information

Table 3. Ordering information

Part number	Package	Material	Packing	Quantity per reel	Flammability rating	Reel size
1SS355	SOD-323	halogen free	tape & reel	3,000pcs	UL 94V-0	7 inches

7. Marking

Table 4. Marking codes

Part number	Marking code
1SS355	A

The marking bar indicates the cathode

Solid dot = Green molding compound device, if none, the normal device.

8. Limiting values and electrical Characteristics

Table 5. Limiting values

$T_a=25^{\circ}\text{C}$





Parameter	Symbol	Limit	Unit
Non-Repetitive Peak Reverse Voltage	V_{RM}	90	V
Peak Repetitive Peak Reverse Voltage	V_{RRM}	80	V
Working Peak Reverse Voltage	V_{RWM}		
DC Blocking Voltage	V_R		
Forward Continuous Current	I_{FM}	225	mA
Average Rectified Output Current	I_O	100	mA
Non-Repetitive Peak Forward Surge Current	I_{FSM}	2.0	A
Power Dissipation	P_d	200	mW
Thermal Resistance from Junction to Ambient	$R_{\theta JA}$	625	$^{\circ}\text{C/W}$
Operation Junction and Storage Temperature Range	T_J, T_{STG}	-55~+150	$^{\circ}\text{C}$

Table 6. Electrical characteristics

$T_a=25^{\circ}\text{C}$


Parameter	Symbol	Min	Typ	Max	Unit	Conditions
Forward voltage	V_F			1.2	V	$I_F=100\text{mA}$
Reverse current	I_{R1}			0.1	μA	$V_R=80\text{V}$
Capacitance between terminals	C_T			3	pF	$V_R=0\text{V}, f=1\text{MHz}$
Reverse recovery time	t_{rr}			4	ns	$I_F=I_R=10\text{mA}$ $V_R=6\text{V} \quad R_L=100\Omega$

9. Typical characteristics



10. Package outline


Table 7. SOD-323 Package outline



Symbol	Dimension in millimeter		
	Min	Nom	Max
A	0.95	1.0	1.05
A1	0.0	0.05	0.1
A2	0.85	0.90	0.95
A3	0.35	0.40	0.45
b	0.30	0.35	0.40
c	0.127	0.131	0.135
D	1.20	1.25	1.30
E	2.50	2.65	2.80
E1	1.65	1.70	1.75
L	0.20	0.30	0.40
L1	0.45		0.65
θ	0°	3°	8°

11. Suggested pad layout

Table 8. Suggested pad layout



Note:

1. Controlling dimension: in millimeters
2. General tolerance: $\pm 0.05\text{mm}$
3. The pad layout is for reference purposes only

12.Disclaimer

CCX PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, SAFETY INFORMATION, AND OTHER RESOURCES “AS IS” AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with CCX products. You are solely responsible for

- (1) selecting the appropriate CCX products for your application;
- (2) designing, validating and testing your application;
- (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements.

These resources are subject to change without notice. CCX grants you permission to use these resources only for development of an application that uses the CCX products described in the resource. Other reproduction and display of these resources are prohibited. No license is granted to any other CCX intellectual property right or to any third party intellectual property right. CCX disclaims responsibility for, and you will fully indemnify CCX and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources. CCX's products are provided subject to CCX's Terms of Sale or other applicable terms available either on www.CCX.com or provided in conjunction with such CCX products. CCX's provision of these resources does not expand or otherwise alter CCX's applicable warranties or warranty disclaimers for CCX products.