

深圳市晶科鑫实业有限公司



样品承认书


客户代码:				
物料名称:	温度补偿晶体振荡器TCX0			
规格型号:	SMD2016 4pin 32.000MHz 1.8V~3.3V ±0.5PPM -30~85℃			
P N/ SJK:	7X32000J13XFH			
环保属性:	☒ RoHS	☒ REACH	☒ HF	☐ PAHS ☐ 其它
版 次:	A1 2025-7-29 初版		最小包装: 3000pcs/real	
湿敏等级:	一级			

e			í € ” ’		
+		!!			!!
☺		Π Ω			
SJK					
FAE_EMAIL					
			E f Ů f Ł Ů		
:					


ELECTRICAL SPECIFICATIONS

Parameters		Condition	Electrical Specifications			
			MIN	TYP	MAX	UNITS
Nominal Frequency			32.000000			MHZ
Operating Temperature Range			-30		85	°C
Supply Voltage			1.68	-	3.63	V
Current Drain					2.0	MA
Output Level			0.8		1.2	Vp-p
Output Type			Clipped sine wave			
Output Load		Resistance	10			kΩ
		Capacitance	10			PF
Frequency Tolerance		After 2times reflow			±2.0	ppm
Frequency Stability	vs:Temperature				±0.5	ppm
	vs:Load	load ±5%			±0.1	ppm
	vs:Supply Voltage	V _{DD} ±5%			±0.1	ppm
Storage Temperature			-40		90	°C
Start-upTime		≥90% of Vpp			2.0	ms
Duty Cycle			40	50	60	%
Harmonics					-5	dBc
Aging					±1.0	ppm/year
Phase Noise		@10Hz offset		-75		dBc/Hz
Phase Noise		@100Hz offset		-100		dBc/Hz
Phase Noise		@1KHz offset		-126		dBc/Hz
Phase Noise		@10KHz offset		-139		dBc/Hz
Phase Noise		@100KHz offset		-144		dBc/Hz


DIMENSION (Unit: mm)




Recommended land pattern



MEASUREMENT CIRCUIT




REFLOW CONDITION




The reflow temperature profile may vary depending on the product model, specifications and frequency range. Refer to the individual product specifications for details


CARRIER TYPE



REEL



RELIABILITY TEST SPECIFICATIONS

Test item	Equipment	Condition	Specification
1.SOLDERABILITY TEST	SJK-REL001、RC-328A	TP:260℃ TsMax: 200℃ TsMin: 150℃ 2 time 	MIL-STD-883E Method 2003.7
2. HERMETICITY TEST	HELIOT-306S	Pressurized 0.4~0.5Mpa ethanol sealed tank for 10 minutes	MIL-STD-883E Method 1014.10
3. VIBRATION TEST	HG-V4、S&A 250B	Enable Crystal(10g) from 10-55-10Hz,X、Y、Z horizontal,1 Minute vibration/time, 1time/ 2 hours.	MIL-STD-883E Method 2007.3
4. MECHANICAL SHOCK	HPC-200、S&A 250B	Enable Crystal 50G(490m/s ²) time=11 ms speed=3.4 m/s half sine wave oscillation	JIS C6701
5. DROP TEST	HARD BOARD.S&A250B	75cm High,3 times on hard board	MIL-STD-202F Method 213B
6. HIGH&LOW TEMP STORAGE TEST(Static test)	H-PTH-80CK & HM101-3ABN, S&A 350B/250B	High temperature: 125℃±2℃,1000hr; Low temperature:-40℃±3℃,1000hrs	MIL-STD883C, METHOD 1011.8
7. TEMP & HUM CYCLING TEST	H-PTH-80CK CHAMBE, S&A 350B/250B	Temperature:-10℃±2℃~65℃±2℃,Humidity:93±3%,1 cycle need 24 hrs. 5cycles.	MIL-STD-883E Method 1005.8
8. HIGH TEM. & HUM.STORAGE TEST	H-PTH-80CK CHAMBE, S&A350B/250B	Temperature:85℃±2, Humidity:85+3,-2%,Store 96 hrs	JIS C6701
9. AGING TEST	H-PTH-80CK CHAMBE, S&A350B/250	Temperature:85℃±2, Store 1000 hrs	JIS C5023

REVISION RECORD (SJK-7X32000MXX04M0J1)

Rev	Revise contents	Reason	Reviser	Checked	Approved
A1	Initial released	--	贺丹斌	李相同	刘惠光