





RoHS




Circuit Diagram




PCB Layout(Pattern Side)



凸柄
Convex handle



短柄贴膜
Short handle film



短柄
Short handle

NOTE:

- 1.Rating: 24V 25mA DC
- 2.Insulation Resistance: $\geq 100 \text{ M}\Omega$
- 3.Withstand voltage: AC 500V 1Minute
- 4.Operating Force Range: 1000gf Max
- 5.Mechanical Life: 3,000 Cycles

Number of digits(位数)	1P	2P	3P	4P	5P	6P	7P	8P	9P	10P	12P
凸柄 Cover/black	DSIC-01LS	DSIC-02LS	DSIC-03LS	DSIC-04LS	DSIC-05LS	DSIC-06LS	DSIC-07LS	DSIC-08LS	DSIC-09LS	DSIC-10LS	DSIC-12LS
短柄 盖子/黑色	DSIC-01LD	DSIC-02LD	DSIC-03LD	DSIC-04LD	DSIC-05LD	DSIC-06LD	DSIC-07LD	DSIC-08LD	DSIC-09LD	DSIC-10LD	DSIC-12LD
短柄贴膜 Short handle film	DSIC-01LF	DSIC-02LF	DSIC-03LF	DSIC-04LF	DSIC-05LF	DSIC-06LF	DSIC-07LF	DSIC-08LF	DSIC-09LF	DSIC-10LF	DSIC-12LF

⑤	Terminal		4	Brass	Gold plating
④	Shrapnel		2	Beryllium copper	Gold plating
③	Handle		2	PA46	White
②	Cover		1	PPS	Black
①	Base		1	PPS	Black
NO.	Name	Number	Qty	Materil	Remarks

ZHONGDI® Zhongdi Electronic Technology Co., Ltd

design	date	name	DIP SWITCH
Review	date	model	DSIC-02LS
Approved	date		
Drawing number:			
Proportion	1:1	unit	mm
gape number			
A4			