

A

B


C

D


E

F

修 订	标 记	修 改 描 要	签 名	日 期
REV NO	MARK	REVISION DESCRIPTION	SIGNATURE	DATE
		NEW DWG		2016-03-12






3D VIEW




NOTES:



- 1.HUOSING: LCP HIGH-TEMP THERMOPLASTIC UL94V-0 COLOR:BEIGE
- 2.ACTUATOR: LCP HIGH-TEMP THERMOPLASTIC UL94V-0 COLOR:BLACK
- 3.TERMINAL:PHOSPHOR BRONZE
PLATING:1*”GOLD FLASH OR 100~150*”TIN(LEAD FREE)
OVERALL 50~100*”NICKEL UNDER PLATED.
- 4.FITTING NAIL:BRASS
PLATING:100~150*”TIN(LEAD FREE)
OVERALL 50~100*”NICKEL UNDER PLATED.



COVER OPEN STATE




CABLE INSERT DIM.



RECOMMENDED PCB PATTERN DIM.

TOLERANCE : ±0.05

APPLICABLE FPC/FFC
(THICKNESS 0.3±0.03)


NO.of contacts	Dimensions				NO.of contacts	Dimensions			
	A.	B.	C.	D.		A.	B.	C.	D.
4	5.80	1.50	2.57	5.00	33	20.30	16.00	17.07	19.50
5	6.30	2.00	3.07	5.50	34	20.80	16.50	17.57	20.00
6	6.80	2.50	3.57	6.00	35	21.30	17.00	18.07	20.50
7	7.30	3.00	4.07	6.50	36	21.80	17.50	18.57	21.00
8	7.80	3.50	4.57	7.00	37	22.30	18.00	19.07	21.50
9	8.30	4.00	5.07	7.50	38	22.80	18.50	19.57	22.00
10	8.80	4.50	5.57	8.00	39	23.30	19.00	20.07	22.50
11	9.30	5.00	6.07	8.50	40	23.80	19.50	20.57	23.00
12	9.80	5.50	6.57	9.00	41	24.30	20.00	21.07	23.50
13	10.30	6.00	7.07	9.50	42	24.80	20.50	21.57	24.00
14	10.80	6.50	7.57	10.00	43	25.30	21.00	22.07	24.50
15	11.30	7.00	8.07	10.50	44	25.80	21.50	22.57	25.00
16	11.80	7.50	8.57	11.00	45	26.30	22.00	23.07	25.50
17	12.30	8.00	9.07	11.50	46	26.80	22.50	23.57	26.00
18	12.80	8.50	9.57	12.00	47	27.30	23.00	24.07	26.50
19	13.30	9.00	10.07	12.50	48	27.80	23.50	24.57	27.00
20	13.80	9.50	10.57	13.00	49	28.30	24.00	25.07	27.50
21	14.30	10.00	11.07	13.50	50	28.80	24.50	25.57	28.00
22	14.80	10.50	11.57	14.00	51	29.30	25.00	26.07	28.50
23	15.30	11.00	12.07	14.50	52	29.80	25.50	26.57	29.00
24	15.80	11.50	12.57	15.00	53	30.30	26.00	27.07	29.50
25	16.30	12.00	13.07	15.50	54	30.80	26.50	27.57	30.00
26	16.80	12.50	13.57	16.00	55	31.30	27.00	28.07	30.50
27	17.30	13.00	14.07	16.50	56	31.80	27.50	28.57	31.00
28	17.80	13.50	14.57	17.00	57	32.30	28.00	29.07	31.50
29	18.30	14.00	15.07	17.50	58	32.80	28.50	29.57	32.00
30	18.80	14.50	15.57	18.00	59	33.30	29.00	30.07	32.50
31	19.30	15.00	16.07	18.50	60	33.80	29.50	30.57	33.00
32	19.80	15.50	16.57	19.00	61	34.30	30.00	31.07	33.50



深圳市华德共创科技有限公司

Shenzhen Huade co-create Technology Co.,LTD

电话: 0755-23304126 传真: 0755-29940187

-TOLERANCES-
UNLESS OTHERWISE SPECIFIED
公差参数表TITLE:
产品名称:FPC0.5间距1.35高掀盖下接带扣

X.X ±0.30 X.X* ±3°

APPD:
核准:PART NO:
产品编号: HDGC0513-xxCL-GF

X.XX ±0.20 X.XX* ±2°

CHECK: 王建业


DATE SCALE UNIT CODE NUMBER

X.XXX ±0.10 X.XXX* ±1°


DRAW: 黄艳兰
绘图:

2016-03-12 1:1 mm A001

修 订	标 记	修 改 描 要	签 名	日 期
REV AO		NEW DWG		2016-03-12




Tape width 16 and 24 mm




PULL OUT DIRECTION

Tape width 32 and 56 mm



PULL OUT DIRECTION

REEL DIM



PULL OUT DIRECTION

No.of	DIM				
Contacts	A	B	C	REEL (CARTON)	SUM(PCS)
4pin~8pin	16	7.5	—	15	60000
9pin~24pin	24	11.5	—	10	40000
25pin~33pin	32	14.2	28.4	8	32000
34pin~54pin	44	20.2	40.4	6	24000
55pin~60pin	56	26.25	52.5	5	20000

NOTES:

- 1.Component load per 13" reel:4000 pcs
- 2.Material: black conductive polystyrene alloy.
- 3.Thickness:0.3±0.05mm
- 4.All dimensions meet EIA-481-C requirements



深圳市华德共创科技有限公司

Shenzhen Huade co-create Technology Co.,LTD

电话: 0755-23304126 传真: 0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表		TITLE: 产品名称: FPC0.5间距1.35高掀盖下接带扣	
X.X ±0.30	X.X* ±3°	APPD: 核准:	PART NO: 产品编号: HDGC0513-xxCL-GF
X.XX ±0.20	X.XX* ±2°	CHECK: 校对: 王建业	DATE
X.XXX ±0.10	X.XXX* ±1°	DRAW: 绘图: 黄艳兰	SCALE
		2016-03-12	UNIT
		1:1	CODE NUMBER
		mm	A001