

**MESSRS.**

---

**SPECIFICATION FOR APPROVAL****承 認 書**

<b>Product</b>	<b>SPEAKER</b>
<b>Part No.</b>	<b>HDK-150808ZA-8P (RoHS)</b>
<b>Customer Approval</b>	

<b>Approved By</b>	<b>Checked By</b>	<b>Made By</b>
王台平 OCT-10-2021	曹丽萍 OCT-10-2021	LILY OCT-10-2021

**常 州 华 龙 电 子 有 限 公 司**

Changzhou Dragon State Electronic Co., Ltd

中国江苏省常州市新区电子园新四路 36 号

Tel: +86-519-85110078. 86-519-85106698, Fax: +86-519-85101081

EDITION:1.1

[illegible]

## 1. Specification

HDK-150808ZA-8P (RoHS)

ITEM		SPECIFICATIONS	
01	Type	Dynamic speaker	
02	Dimension	External diameter 15*8 mm	
03	Rated Input Power	0.8W In 1cc Box	
04	Max. Input Power	1.0W In 1cc Box For 1 Minute	
05	Impedance	8ohm $\pm$ 15% at 2000Hz.	
06	Resonance Frequency (Fo)	1000Hz $\pm$ 20% at In 1cc Box	
07	Sensitivity (S.P.L.)	90 $\pm$ 3 dB SPL/1.0W/0.1M	at 1000Hz in 1cc box
08	Frequency Range	Fo – 20KHz	
09	Total Harmonics Distortion	Max 8% at 1 KHz, 1.0W.	
10	Weight	1.5g $\pm$ 5%g	
11	Appearance	Should not exist any obstacle to be harmful to normal operation; damages, cracks, rusts and distortions, etc.	
12	Operation Test	Must be normal at program source – 0.8W	
13	Buzz, Rattle, etc.	Must be normal at sine wave 0.89Vrms (in free air) /2.53Vrms(in 1.0cc box) from 300~3400Hz	
14	Polarity	When positive voltage is applied to the terminal marked (+), diaphragm should move to the front.	
15	Terminal Strength	Capable of withstand 1kg load for 30 seconds without resulting in any damage or rejection.	
16	Temperature	Operating temperature: -30℃ to +70℃ Storage temperature: -30℃ to +70℃	

## 2-1. Test Condition Standard

Temperature : 15 ~ 35°C

Relative humidity : 25% ~ 85%,

Atmospheric pressure : 860mbar to 1060mbar.

### Basic

Temperature : 20±3°C

Relative humidity : 60% ~ 70%

Atmospheric pressure : 860mbar to 1060mbar

## 2-2. Standard Test Fixture


1.Input Power :1.0W ( 2.83V )

2.Zero Level : -dB


3.Mode : SPEAKER

4.potentiometer Range : 50dB


5.Sweep Time : 0.5sec



## 2-3. Frequency Response Curve




**FR**




**THD**

### 3. Dimension



## 4. Reliability Test








Items.		Specifications
01	High temp. Test	Keep 96 hours at $+70^{\circ}\text{C}\pm 3^{\circ}\text{C}$ and leave 3 hours in normal temperature and then check
02	Low temp. Test	Keep 96 hours at $-40^{\circ}\text{C}\pm 3^{\circ}\text{C}$ and leave 3 hours in normal temperature and then check
03	Humidity test	Keep 96 hours at $+40^{\circ}\text{C}\pm 3^{\circ}\text{C}$ relative humidity 95% and leave 3 hours in normal temperature and then checked.
04	Temp./Humidity cycle	<p>The part shall be subjected 5 cycles. One cycle shall be 12 hours and consist of;</p> 
05	Thermal cycle test.	Low temperature: $-40^{\circ}\text{C}\pm 3^{\circ}\text{C}$ , temperature: $+70^{\circ}\text{C}\pm 3^{\circ}\text{C}$ , cycle: 1 hour/cycle each, and then keep 5 cycles in a room.
06	Vibration	10~200~10Hz sin-wave sweep 15min. 5G(constant) X,Y, Z 3 direction. 2 hours each, total 6 hours.
07	Fix drop test	Fix on jig. Then drop from 152cm height to the concrete floor X, y, z 6 direction. 5 times each, total 30 times.
08	Free drop test	Free drop from 100cm height to the concrete floor X, y, z 6 direction. 1 times each, total 6 times.
09	Rated Power test	Rated Power white noise is applied for 96 hours In 1cc Box
10	Max Power test	Max power 1 min on – 2 min off 10 cycles.
11	Terminal strength test	Capable of withstand 1kg load for 30 seconds without resulting in any damage or rejection.
12	Protection against liquids	Protected against 1hour of immersion under 1.5M pressure
<b>Criterion: After these test , the change of S.P.L shall be within <math>\pm 3</math> dB .</b>		

### Soldering Condition

Recommend using constant branding iron in **15 ~ 30W**, and in temperature range **350  $\pm 10^{\circ}\text{C}$** .

Soldering time not over **3** seconds.

## 5. Packing

REV NO.	REVISION NOTE	APPROVAL	DATE
	<div style="text-align: center;">  </div> <div style="text-align: right; margin-top: 10px;">           Cover(290*225*3mm) Material: Paper         </div>		
	<div style="text-align: center;">  </div> <div style="text-align: center;">  </div> <div style="text-align: right; margin-top: 10px;">           Box(290*225*10mm) 100pcs Material: Paper+Epe         </div>		
	<div style="text-align: center;">  </div> <div style="text-align: center;">  </div> <div style="text-align: right; margin-top: 10px;">           Middle(290*225*135mm) 1000pcs(10*100pcs) Material: Paper+Epe         </div>		
	<div style="text-align: center;">  </div> <div style="text-align: center;">  </div> <div style="text-align: right; margin-top: 10px;">           Outer Box(515*320*280mm) 4000pcs(4*1000pcs) Material: Paper         </div>		
单位: mm			
TITLE: Packing		DRAWN: Lily      2016/08/18      SCALE: 2:1      SHEET: 1 of 1	
PART NO.	1	DESIGNED: R&D OF D.S.	UNITS: mm
		CHECKED: Emily	TOLERANCE
DWG NO.		APPROVAL: Eric	20~11      ± 0.3
	REV	MATERIAL:	10~5      ± 0.2
			<4      ± 0.1
<div style="display: inline-block; border: 1px solid black; padding: 5px; margin-right: 10px;">DS</div> Changzhou Dragon State Electronic Co., Ltd			