


修 订	标 记	修 改 描 要	签 名	日 期
REV A0		NEW DWG		2016-03-12

NOTES:

- 1.HUOSING: LCP HIGH-TEMP THERMOPLASTIC UL94V-0 COLOR:NATURE
- 2.ACTUATOR: LCP HIGH-TEMP THERMOPLASTIC UL94V-0 COLOR:BLACK
- 3.TERMINAL:PHOSPHOR BRONZE C5191
PLATING:GOLD FLASH OVERALL 50~100μ" NICKEL UNDER PLATED.
- 4.FITTING NAIL:PHOSPHOR BRONZE C5191
PLATING:100~150μ" TIN(LEAD FREE)
OVERALL 50~100μ" NICKEL UNDER PLATED.

- 5.SPECIFICATION:
CURRENT RATING: 0.5A 50V AC/DC
CONTACT RESISTANCE: 30mΩ MAX
INSULATION RESISTANCE: 100MΩ AT 500V DC
OPERATING TEMPERATURE RANGE: -40°C~85°C
WITHSTANDING VOLTANG: 500V AC/minute



NO.of contacts	Dimensions				
	A.	B.	C.	D.	F.
30	22.00	14.50	19.10	22.29	7.35
41	27.50	20.00	24.60	27.79	10.00
51	32.50	25.00	29.60	32.79	10.00





深圳市华德共创科技有限公司






Shenzhen Huade co-create Technology Co.,LTD

电话: 0755-23304126 传真: 0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表				TITLE: 产品名称: FPC0.5间距2.2高掀盖式带扣B款			
X.X	±0.30	X.X*	±3°	APPD: 核准:	PART NO: 产品编号: HDGC0527B-xxCL-GF		
X.XX	±0.20	X.XX*	±2°	CHECK: 校对: 王建业	DATE	SCALE	UNIT
X.XXX	±0.10	X.XXX*	±1°	DRAW: 绘图: 黄艳兰	2016-03-12	1:1	mm
				CODE NUMBER A001			





COVER OPEN STATE





RECOMMENDED PCB PATTERN DIM.

TOLERANCE : ±0.05

F		F		F	
修	标	修	签	日	
订	记	改	名	期	
REV	MARK	REVISION DESCRIPTION	SIGNATURE	DATE	
AO		NEW DWG		2016-03-12	



APPLICABLE FPC/FFC
蓝白裸线（不接地）



APPLICABLE FPC/FFC
一体补强板铝箔FFC线

一体补强板铝箔FFC线

NO.of contacts	Dimensions	
	B.	E.
30	14.50	19.05
41	20.00	24.55
51	25.00	29.55



深圳市华德共创科技有限公司
Shenzhen Huade co-create Technology Co.,LTD
电话: 0755-23304126 传真: 0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表				TITLE: 产品名称: FPC0.5间距2.2高掀盖式带扣B款			
X.X	±0.30	X.X*	±3°	APPD: 核准:	PART NO: 产品编号: HDGC0527B-xxCL-GF		
X.XX	±0.20	X.XX*	±2°	CHECK: 校对: 王建业	DATE	SCALE	UNIT
X.XXX	±0.10	X.XXX*	±1°	DRAW: 绘图: 黄艳兰	2016-03-12	1:1	mm