




| A | B | C | D | E | F |
|--------------|------------|------------------------------|-----------------|------------|---|
| 修订 REV A0 | 标记 MARK | 修改摘要 REVISION DESCRIPTION | 签名 SIGNATURE | 日期 DATE | |
| NEW DWG | | 2016-03-12 | | | |





NOTES:

- HUOSING: LCP HIGH-TEMP THERMOPLASTIC UL94V-0 COLOR:NATURE
- ACTUATOR: LCP HIGH-TEMP THERMOPLASTIC UL94V-0 COLOR:BLACK
- TERMINAL:PHOSPHOR BRONZE
PLATING:1µ" GOLD FLASH OR 100~150µ" TIN(LEAD FREE)
OVERALL 50~100µ" NICKEL UNDER PLATED.
- FITTING NAIL:PHOSPHOR BRONZE
PLATING:100~150µ" TIN(LEAD FREE)
OVERALL 50~100µ" NICKEL UNDER PLATED.


5.SPECIFICATION:
CURRENT RATING: 0.5A 50V AC/DC
CONTACT RESISTANCE: 30mΩ MAX
INSULATION RESISTANCE: 100MΩ AT 500V DC
OPERATING TEMPERATURE RANGE: -40°C~85°C
WITHSTANDING VOLTAGE: 500V AC/minute



CABLE INSERT DIM.
SCALE 2:1



| NO.of contacts | Dimensions | | | | |
|-------------------|------------|-------|-------|-------|-------|
| | A. | B. | C. | D. | E. |
| 60 | 37.00 | 29.50 | 37.24 | 34.10 | 32.60 |
| 68 | 41.00 | 33.50 | 41.24 | 38.10 | 36.60 |
| 80 | 47.00 | 39.50 | 47.24 | 44.10 | 42.60 |
| 96 | 55.00 | 47.50 | 55.24 | 52.10 | 50.60 |



RECOMMENDED PCB PATTERN DIM.


TOLERANCE : ±0.05



深圳市华德共创科技有限公司
Shenzhen Huade co-create Technology Co., LTD
电话: 0755-23304126 传真: 0755-29940187


| -TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表 | | APPD* 核准: | TITLE: 产品名称: FPCO.5间距2.1高掀盖下接带扣 | | |
|---|-------|--------------|------------------------------------|------------|--------|
| X.X | ±0.30 | X.X* ±3° | CHECK: 校对: | DATE | SCALE |
| X.XX | ±0.20 | X.XX* ±2° | DRAW: 绘图: | 2016-03-12 | 1:1 mm |
| X.XXX | ±0.10 | X.XXX* ±1° | 黄艳兰 | | A001 |

| A | B | C | D | E | F |
|-----------------|------------|------------------------------|-----------------|------------|---|
| 修订 REV AO | 标记 MARK | 修改摘要 REVISION DESCRIPTION | 签名 SIGNATURE | 日期 DATE | |
| | | NEW DWG | | 2016-03-12 | |



APPLICABLE FPC/FFC

蓝白裸线（不接地）



APPLICABLE FPC/FFC

一体补强板铝箔FFC线

| NO.of contacts | Dimensions | | | |
|----------------|------------|-------|-------|-------|
| | B. | E. | F. | G. |
| 60 | 29.50 | 34.05 | 35.00 | 32.55 |
| 68 | 33.50 | 38.05 | 39.00 | 36.55 |
| 80 | 39.50 | 44.05 | 45.00 | 42.55 |
| 96 | 47.50 | 52.05 | 53.00 | 50.55 |



深圳市华德共创科技有限公司

Shenzhen Huade co-create Technology Co., LTD

电话: 0755-23304126 传真: 0755-29940187

| -TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表 | | APPD: 核准: | TITLE: 产品名称: FPCO.5间距2.1高掀盖下接带扣 | | | | | |
|---|-------|--------------|------------------------------------|---------------|------------|-------|------|-------------|
| X.X | ±0.30 | X.X* | ±3° | CHECK: 校对: | DATE | SCALE | UNIT | CODE NUMBER |
| X.XX | ±0.20 | X.XX* | ±2° | 王建业 | | | | |
| X.XXX | ±0.10 | X.XXX* | ±1° | 黄艳兰 | 2016-03-12 | 1:1 | mm | A001 |

