







- 1.CIRCUIT : ON/OFF (复位)
2." $\bigcirc$ "DENOTES CRITICAL DIMENSIONS.
3.Operation force : 800±300gf
4.RATING:16A 125/250VAC 3/4HP 125/250VAC(CUL)
16(4)A 125/250V~ T125/55(ENEC17;NEMKO;CB)
16(4)A 250~ T125/55(CQC)
C-UL APPROVAL FILE NO.E153399
ENEC17 CERTIFICATE NO.3689
NEMKO CERTIFICATE NO.P10213218/A2
CQC CERTIFICATE NO.CQC10002051908
CB APPROVAL FILE NO.60225/A1/M1

- 5.Contact resistance : <50m Ω
6.Insulation resistance : >100M Ω (500VDC between open contacts)
7.Dielectric strength : >1500Vac 0.5mA 1 minute
8.ACTUATOR COLOR:WHITE
HOUSING COLOR:WHITE
BASE COLOR:BLACK
9.ALL MATERIALS ARE ROHS COMPLIANT

TEL : 0769-82310511-867



PANEL CUTOUT DIMENSION:



5	→	10	→	DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN	MM				
4	→	9	→	RANGE	TOLERANCE	LMC 2018. 01. 16			LMC 2017. 05. 24	SCALE	NO				
3	→	8	→	X	±0.3					MAT'L	***				
2	→	7	→	X.X	±0.2					MATERIAL NO.		DRAWING NO.	REV.		
1	→	6	→	X.XX	±0.1					LEGION ELECTRONIC & HARDWARE CO., LTD.				MPS21-WWBCB-S1M-A	
NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±1'										