

SPECIFICATIONS

Rated Current:3.0AMP

Contact Resistance: 20m Ω Max

Withstand Voltage:1000V AC/DC

Insulation Resistance: 1000M Ω Min

Operation Temperature: -40°C to $+105^{\circ}\text{C}$

Contact Material: Brass



Contact Plating: Au Or Tin Over Ni

Insulator Material: Polyester (UL94V-0)

Standard: PA6T

Max.Processing Temp: 230°C for 30-60 seconds

(260°C for 10 seconds)





Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE $\pm$ 0.05)

P	X	X	X	X	X	X			
产品类型 P=材料	厚度 A=1.27 B=1.0 C=2.0 D=2.5 E=3.6 F=5.0 A=12.7	塑胶板 A=1.0 B=1.5 C=2.0 D=2.5 E=3.6 F=5.0	材料 1=单排 2=双排 3=三排 4=四排	单排IN数 1~40P	产品形态 1=RA 2=SA 3=ST 4=SH 5=模切板	塑胶材料 1=BHT 2=LCP 3=PS 4=PA66 5=PA6T 9=PA9T	电镀厚度 00=薄镀 01=中镀 02=厚镀 03=3μ" 04=4μ"	包装方式 1=管装 2=卷装 3=盘装 4=袋装 5=盒装	序列号 XXXXXX

Dimension antitheses list								
ITEM	PA	PB	PC	L1	L2	L3	H	W
001	6.00	4.30	3.00	13.80			2.5	2.5
Alternate								

Ordering Information



深圳市连盛精密连接器有限公司									
PART NO.		1010301719							
TITLE:		2.54PH 1XNP 90度							
PROJ.	SCALE	FIT							
UNIT	mm								
SIZE	A4								
SHEET	1/1								
APPROVE									
CHECK									
X.XX	±0.20								
X.XXX	±0.10								
Angle	±3°								
DIM	TOL								
CHANGE									
MODIFICATION DESCRIPTION									
DATE									
REV									

深圳市连盛精密连接器有限公司

PART NO.	1010301719
----------	------------

TITLE: 2.54PH 1XNP 90度