



# RoHS

Recommended P.C.B Layout(Top Side)  
(PCB BOARD TOLERANCE±0.05)

## SPECIFICATIONS

Rated Current:3.0AMP  
Contact Resistance:20mΩ Max  
Withstand Voltage:1000V AC/DC  
Insulation Resistance:1000MΩ Min  
Operation Temperature:-40°C to +105°C



Contact Material:Brass  
Contact Plating:Au Or Tin Over Ni  
Insulator Material:Polyester(UL94V-0)  
Standard: PA6T  
Max.Processing Temp: 230°C for 30-60 seconds  
(260°C for 10 seconds)



## Ordering Information

P X X X X XX X X XX X XXX

产品型号 间距 塑胶数量 封装 异形N数 产品型号 塑胶材料 电镀厚度 包装方式 序列号  
P=材料 1=1.27 A=1.0 1=单排 1~40P 1=DIP 1=FBT 00=常规 1=常规  
2=2.0 B=1.5 2=双排 1~40P 2=RA 2=LCP 01=1u" 2=通插  
3=2.54 C=2.0 3=三排 3=PPS 02=2u" 3=通插  
4=3.96 D=2.5 4=四排 4=PA46 03=3u" 4=通插  
5=1.27\*2.54 A=1.27\*2.54 5=机械脚 9=PA9T 5=通插



Dimension antitheses list									
ITEM	PA	PB	PW	L1	L2	L3	H	W	
001	6.00	3.20	5.00	11.00			2.5	2.5	
Alternate									

深圳市连盛精密连接器有限公司

OPERATION		DRAW		SCALE		FIT	
X.X	±0.30			UNIT	mm	SIZE	A4
X.XX	±0.20	CHECK		SHEET	1/1	PART NO.	1010301747
X.XXX	±0.10	APPROVE		PROJ.		TITLE:	2.54PH 1XNP SMT
Angle	±5°						
DIM	TOL						

REV	DATE	MODIFICATION DESCRIPTION	CHANGE
A0	2012.03.28	NEW DRAWING	

1	2	3	4	5	6	7	8	9
---	---	---	---	---	---	---	---	---