







RoHS



SIM pin assignment	
PIN#	Name
C1	VCC供电电压
C2	RST重置
C3	CLK时钟
C5	GND接地
C6	VPP程序电压
C7	I/O输入输出



RECOMMENDED P.C.B HOLE LAYOUT
COMPONENT SIDE VIEW(TOLERANCE: +/-0.05)

PCB 焊盘区
下沉避让区

Product No. : MICRO-SIM-0003

型号: 包装方式
-P=编带 (非编带, 不启用)

Specifications/技术规格:

- 1.Current rating/ 额定电流: 0.5mA
- 2.Voltage rating/ 额定电压: 50V AC/DC
- 3.Insulation Resistance/ 绝缘电阻: 100MΩ Min
- 4.Dielectric Withstanding/ 耐电压: 500V AC/minute
- 5.Contact Resistance/ 接触电阻: 100mΩ Max
- 6.Durability/ 耐久性: 5,000 Insertions
- 7.Operating Temperature/ 工作温度: -40℃ to +85℃

⑤	Spring		1	SUS	Ni Plated
④	Contact point		6	Phosphor bronze	Au Plated
③	Terminal		6	Phosphor bronze	Sn Plated
②	Cover		1	SUS	
①	Base		1	LCP	Black
NO.	Name	Number	Qty	Materil	Remarks




ZHONGDI® Zhongdi Electronic Technology Co., Ltd

design	date	name	MICRO SIM CARD CONNECTOR
Review	date	model	MICRO-SIM-0003
Approved	date		


Drawing number: A4

RoHS



客户拉出方向



客户拉出方向



上封盖带
300 MM MIN



ZHONGDI® Zhongdi Electronic Technology Co., Ltd

design	date	name	MICRO SIM CARD CONNECTOR
Review	date	model	MICRO-SIM-0003
Approved	date		

Drawing number: Proportion 1:1 unit mm gage number A4

modify Review Approved

Tolerance not specified