





REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	ECR-15-013750	19SEP2015	DW	CW
	B1	ECR-15-016224	05NOV2015	DW	CW
	C	ECR-20-016101	09JUN2021	BS	CW
	D	ECR-25-246907	18JUN2025	ABS	RB




M3 SCREW,
RECOMMENDED
TIGHTENING
TORQUE 0.5Nm

NOTES:
1. TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: 400 V
RATED CURRENT: 10 A
INSULATION RESISTANCE: $\geq 400M\Omega$
RATED IMPULSE VOLTAGE: 6 kV
POLLUTION DEGREE: 3
FLAMMABILITY: UL94V-0
MATING CYCLES: 500 CYCLES
WIRE RANGE: 0.5-2.5 mm² (20-14 AWG)
CONTACT FINISH: SILVER PLATED
CONTACT TYPE: SPRING CONTACT

注释:
1. 技术参数:
绝缘材料: PC
额定电压: 400V
额定电流: 10A
绝缘电阻: $\geq 400M\Omega$
额定脉冲电压: 6 kV
污染等级: 3
阻燃等级: UL94V-0
插拔次数: 500 次
接线范围: 0.5-2.5 mm² (20-14 AWG)
端子表面处理: 镀银
接线类型: 弹片压接



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DAVID WANG 17MAR2015	TE Connectivity									
		CHK CHRIS WANG 17MAR2015										
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD XU XIANG 17MAR2015	NAME HA-003-MS									
	0 PLC ±-	PRODUCT SPEC	SIZE A3				CAGE CODE 00779	DRAWING NO C-T2010033101000	RESTRICTED TO -			
	1 PLC ±-	108-137045										
	2 PLC ±-	APPLICATION SPEC										
	3 PLC ±-	114-137045										
	4 PLC ±-	WEIGHT										
	ANGLES ±-	-										
MATERIAL	FINISH											
-	-											
-	-											
CUSTOMER DRAWING			SCALE		2:1		SHEET		1 OF 1		REV	D