


SPECIFICATION

1.Material:

Housing: LCP S475, Rated UL94V-0,Color:Black.
Contacts: C7025 TM03
Matte Tin 80u"MIN. at Solder Tail,
Plating 15U" on Contact Area.Over Nickle 50u"MIN.
Shell: SUS304 1/2H.
Goldflash at Solder Tail,Over Nickel 30u"MIN.Plated.
LOCK PIN: SUS304 3/4H. Not Plating.
SPRING: SWP-B. Not Plating.
CAM ROD: SUS304H. Not Plating.

2.Electrical Characteristics:

Rated voltage : 500Vrms AC for 1 min.
Current rating : 1.0 A.Min.per pin.
Operating Temperature: -25°C~+85°C.
Insulation resistance: 1000M ohms Min. at 500VDC for 1ms.
Dielectric withstanding voltage:500 VAC/1minute.
Contact resistance: Initial:55m ohms max. Final: Δ40m ohms max.
Insertion Force: 25N Max.
Removal Force: 0.5N Min. 20N Max.
Inverse Insertion: 50N Min.
Mating cycle: 10000 cycles, Spring is not breaking.



深圳市华宇创精密电子有限公司

TOLERANCE:

XX ±0.30
XX ±0.25
XXX ±0.15
X° ±2° X.X° ±0.5°

UNIT: mm [inch]
SCALE:1:1 SIZE: A4

DRAWN BY :

陈一鸣

DATE :

2014-02-23

PART NAME:

CF Express Type A NO PUSH CONN. 外壳两脚

CHECKED BY:

马跃

DATE :

2014-02-23

PART NO.

HYCW35-CF13-375B

MOLD NO.

APPROVED BY:

邱敏

DATE :

2014-02-23

DRAW NO:

HYC-2404301528

SHEET NO.

1 OF 1