





3D VIEW



RECOMMENDED PCB LAYOUT

TOLERANCE: ± 0.05 

WORKING STATE



1. MATERIAL SPECIFICATION:
 1.1. C5240 T=0.10 $\pm$ 0.005MM
2. TEST REQUIREMENTS:
 2.1. CONTACT RESISTANCE: 50m Ω MAX
 2.2. VOLTAGE RATING: 10.0V/AC/DC/MAX
 2.3. RATED CURRENT: 2.0A/MAX
 2.5. WELDING THRUST: ≥ 3.0 Kg
 2.6. DURABILITY: 3,000 TIMES
 2.7. OPERATING TEMPERATURE: -20 ° ~ 80 ° C
3. PLATING REQUIREMENTS:
 3.1. THE NICKEL-PLATED SUBSTRATE IS 50U MIN,
 3.2. SALT SPRAY TEST TO MEET THE REQUIREMENTS OF 24 HOURS.
 3.3. TERMINAL TO EAT FULL TIN, NOT PEELING, WELDING OBVIOUS COLOR AND OTHER ADVERSE
 3.4. ROHS, REACH, HF HALOGEN-FREE AND A SERIES OF DOMESTIC AND INTERNATIONAL ENVIRONMENTAL REQUIREMENTS



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ± 0.30 X.XX ± 0.25 X.XXX ± 0.15 X' $\pm 2'$ X.X' $\pm 0.5'$	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 天线弹片 L2.60*W1.00*H1.60
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW-TXT261016A
UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO: HYC-2412301011
			SHEET NO. 1 OF 1