

F

E

D

C

B

A

F







E

D

C

B

A



P.C.B LAYOUT(TOL:±0.05)

规格说明: Specifications:
电气特性: Electrical:
1.额定电流: Current Rating
1A/contact terminal
2.额定电压: Voltage Rating
30V DC
3.接触阻抗: Contact Resistance
30 milliohms MAX
4.耐电压: Dielectric Withstanding
Voltage
500 V AC AT Sea Level
5.绝缘阻抗: Insulation Resistance
1000MEGA ohms MIN
物理性能: Mechanical:
1.插拔力: Connector Mate and Unmate Force
Mate force: 35N (MAX)
Unmate force: 7N (MIN)
材料: Material:
1.塑胶: Housing:
PBT
2.端子: Contact:
Copper Alloy C2680
3.外壳: Shell:
SPCC
电镀Finish:
1.端子: Contact:
Plated Gold in Mating Area,
Tin On Solder Tails
2.外壳: Shell
Nickel Plating
温度范围: Temperature Range:
-30°C to +80°C

TOLERANCE UNLESS OTHERWISE SPECIFIED
.XXX ±0.10
.XX ±0.20
.X ±0.30
.X* ±3°

产品名称	AM 18度	
PART NAME:		
料号	see table	C
PART No:		

REV:	DESCRIPTION	REV BY	APPROVED	DATE	MATL:	SEE SPECIFICATION	APPROVED	罗小春
					PROJECTION:	THIRD ANGLE PROJECTION	CHECKED	张伟
					UNIT:	SCALE	REV(NO)	SHEET
					mm	1:1	A	1 OF 1
							DATE	2020.7.9