






3D VIEW



RECOMMENDED PCB LAYOUT
TOLERANCE: ±0.05



RECOMMENDED METAL MASK
TOLERANCE: ±0.05

1. MATERIAL SPECIFICATION:
1.1. STAINLESS STEEL SUS-301 T=0.10±0.005MM
2. TEST REQUIREMENTS:
2.1. CONTACT RESISTANCE: 80mΩ MAX
2.2. VOLTAGE RATING: 1.5 V/AC/DC/MAX
2.3. RATED CURRENT: 1.0A/MAX
2.4. WELDING THRUST: ≥3.0 Kg
2.5. DURABILITY: 1,500 TIMES
2.6. OPERATING TEMPERATURE: -20 ° ~ 80 ° C
3. PLATING REQUIREMENTS:
3.1. THE NICKEL-PLATED SUBSTRATE IS 50U MIN.
3.2. SALT SPRAY TEST TO MEET THE REQUIREMENTS OF 24 HOURS.
3.3. TERMINAL TO EAT FULL TIN, NOT PEELING, WELDING, OBVIOUS COLOR AND OTHER ADVERSE
3.4. ROHS, REACH, HF HALOGEN-FREE AND A SERIES OF DOMESTIC AND INTERNATIONAL ENVIRONMENTAL REQUIREMENTS



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X.' ±2" X.X' ±0.5'	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 天线弹片 L3.50*W1.00*H1.20
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW-TXT351012
UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO: HYC-2412271206
			SHEET NO. 1 OF 1