






RECOMMEND PCB LAYOUT
TOLERANCE:±0.05

NO.	SPEC	Q'TY
1	HOUSING	1
2	TERMINAL	n
3	FITTING-NAIL	2
4	COVER	1




SECTION A-A



说明:

1. 产品表面清洁,无锈蚀、氧化、裂纹、缺芯、毛刺、及其它机械损伤;
2. 塑胶材料:LCP UL94V-0,颜色:本色;
3. 焊片:黄铜,镀底30u"Min.,镀锡50u"Min.;
4. 接触针:黄铜,镀底30u"Min.,镀锡50u"Min.;
5. 满足灼热丝温度850度.
6. 工作温度-40~+85°C
7. 额定电流:1A AC/DC
8. 额定电压:125V AC/DC
9. 接触阻抗:20mΩ Max.
10. 绝缘阻抗:500MΩ Min.
11. 耐电压:250V AC FOR 1 MINUTE



P/N	PIN	DIM A	DIM B	DIM C
BX-MX1.25-2PLT-XM	2	1.25	7.25	3.05
BX-MX1.25-3PLT-XM	3	2.50	8.50	4.30
BX-MX1.25-4PLT-XM	4	3.75	9.75	5.55
BX-MX1.25-5PLT-XM	5	5.00	11.00	6.80
BX-MX1.25-6PLT-XM	6	6.25	12.25	8.05
BX-MX1.25-7PLT-XM	7	7.50	13.50	9.30
BX-MX1.25-8PLT-XM	8	8.75	14.75	10.55
BX-MX1.25-9PLT-XM	9	10.00	16.00	11.80
BX-MX1.25-10PLT-XM	10	11.25	17.25	13.05
BX-MX1.25-11PLT-XM	11	12.50	18.50	14.30
BX-MX1.25-12PLT-XM	12	13.75	19.75	15.55
BX-MX1.25-13PLT-XM	13	15.00	21.00	16.80
BX-MX1.25-14PLT-XM	14	16.25	22.25	18.05
BX-MX1.25-15PLT-XM	15	17.50	23.50	19.30
BX-MX1.25-16PLT-XM	16	18.75	24.75	20.55
BX-MX1.25-17PLT-XM	17	20.00	26.00	21.80
BX-MX1.25-18PLT-XM	18	21.25	27.25	23.05
BX-MX1.25-19PLT-XM	19	22.50	28.50	24.30
BX-MX1.25-20PLT-XM	20	23.75	29.75	25.55

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA			料号 PART NO.	BX-MX1.25-NPLT-XM		版本 REV.	A
			X.±0.30	X°.±5°	审核 CHECK	EVA			品名 TITLE	1.25-NP立贴窗口加盖 卷装,亮锡,LCP		页次 SHEET	1/1
			.X±0.25	X.X°.±3°	核准 APPROVAL	JADE			客户料号 CUTM.NO.				
			.XX±0.20	X.XX°.±1°	单位 UNITS	MM	比例 SCALE	1:1	 Bossie (博锡)				