






REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A	Ⓐ1 X2	图面升级整理图面	2025.08.06	阿树





P.C.B LAYOUT



SPECIFICATION

Contact Rating: 50mA,12V DC
Contact Resistance: 100mΩ max
Insulation Resistance: 100MΩ min.500V DC
Dielectric Strength: 250V AC/1minute
Operating force: 180gf±50gf
Operating life: 50,000 cycles

PAPT NO	TS-1101NH-X-X-B
Operating Force	B:160gf C:260gf
Height	H:A:4.3 B:5.0
Position Foot	B:black



Circuit Diagram

⑤	Terminal	2	H65	Ag Plating
④	Housing	1	PA6T	
③	Contact form	1	SUS	Ag Plating
②	Cover	1	Cold rolled steel	
①	Stem	1	PA6T	
ITEM	PAPT NAMF	QTY	MATERIAL	FINISHING

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	







DESIGN
CHECKED
APPROVED

阿树

VIEW:
UNIT: mm/in
SIZE: A4

MODEL TYPE:
TACT SWITCH
PART NO.:
TS-1101NH-X-X-X
DWG NO.:

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.08.06	阿树



PAPT NO	TS-1101NH-C-B-W
Operating Force	C:260gf
Height	B:5.0
Position Foot	W:White

⑤	Cards	1	Brass 0.2	
④	Stem	1	PPA	White
③	Cover	1	Fe 0.25	Copper tin plated
②	Contact form	1	SUS	Ag Plating
①	Housing	1	PPA	White
ITEM	PAPT NAMF	QTY	MATERIAL	FINISHING

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAUCES	



DESIGN	阿树
CHECKED	
APPROVED	

VIEW:	
UNIT:	mm/in
SIZE:	A4

MODEL TYPE:	TACT SWITCH
PART NO.:	TS-1101NH-X-X-X
DWG NO.:	