




P.C.B LAYOUT
TOLERANCE: ± 0.05



- 1.MATERIAL SPECIFICATION:
1.1.C5191 EH T=0.15 $\pm$ 0.005MM
2.TEST REQUIREMENTS:
2.1.CONTACT RESISTANCE: 80m Ω MAX
2.2.VOLTAGE RATING: 1.5 V/AC/DC/MAX
2.3.RATED CURRENT: 1.0A/MAX
2.4.WELDING THRUST: ≥ 3.0 Kg
2.5.DURABILITY: 1,500 TIMES
2.6.OPERATING TEMPERATURE: -20 ° ~ 80 ° C
3.PLATING REQUIREMENTS:
3.1.THE NICKEL-PLATED SUBSTRATE IS 50U MIN,
3.2.SALT SPRAY TEST TO MEET THE REQUIREMENTS OF 24 HOURS.
3.3.TERMINAL TO EAT FULL TIN, NOT PEELING, WELDING,
OBVIOUS COLOR AND OTHER ADVERSE
3.4.ROHS, REACH, HF HALOGEN-FREE AND A SERIES
OF DOMESTIC AND INTERNATIONAL ENVIRONMENTAL
REQUIREMENTS



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ± 0.30 X.XX ± 0.25 X.XXX ± 0.15 X.' $\pm 2'$ X.X' $\pm 0.5'$	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 天线弹片 L4.00*W1.50*H3.25	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW-TXT4015325A	MOLD NO.
 UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO: HYC-2412301601	SHEET NO. 1 OF 1