








REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A	Ⓐ1X7	尺寸变更, 图面升级整理图面	2025.04.15	阿树



P.C.B LAYOUT
BOTTOM VIEW



SCHEMATIC (NON-SHORTING)



- Specifications (规格):
1. Rated load (额定负载): DC 50V 0.5A
 2. Contact resistance (接触电阻): $\geq 100\text{m}\Omega$ Max
 3. Insulation resistance (绝缘电阻): $\leq 100\text{M}\Omega$ Min
 4. Withstanding voltage (耐压值): 500V AC/minute
 5. Intensity (力度): $250 \pm 100\text{gf}$
 6. Mating cycles (使用寿命): 5000 cycles Min
 7. Hand welding (手焊温度): $350^\circ\text{C} \sim \pm 10^\circ\text{C}$

6	Spring	Steel Wire	1	Natural
5	Contact	Brass Strip	1	Ag Plated
4	Terminal	Brass Strip	3	Ag Plated
3	Base	Phenolic Resin	1	Natural
2	Frame	Steel Strip	1	Black
1	Knob	Pom	1	Black
NO.	PARTS	MATERIAL	Q'TY	FINISH

AuGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEWS	MODEL TYPE: SLIDE SWITCH
CHECKED		UNIT: mm/in	PART NO.: SS12F55X
APPROVED		SIZE: A4	DWG NO.: