


1、Physical Dimensions(size of 0805)

Unit:mm

Part Number	A		B		C		D	Marking
	Min	Max	Min	Max	Min	Max		
K0805L020/24AR	2.0	2.3	1.2	1.5	0.60	1.00	0.20	2



2、Electrical Characteristics

Part Number	I _H (A)	I _T (A)	V _{max} (V)	I _{max} (A)	T _{trip} (Max time to trip)		Pd _{typ} (W)	R _{min} (Ω)	R1 _{max} (Ω)
					Current(A)	Time(S)			
K0805L020/24AR	0.20	0.50	24	100	8.0	0.02	0.60	0.50	3.20

I_H: Holding Current: maximum current at which the device will not trip in 25°C still air.

I_T: Tripping Current minimum current at which the device will trip in 25°C still air.

V_{max}: Maximum voltage device can withstand without damage at rated current.

I_{max}: Maximum fault current device can withstand without damage at rated voltage.

T_{trip}: Maximum time to trip(s) at assigned current.

Pd_{typ}: Rated working power.

R_{min}: Minimum resistance of device prior to trip at 25°C.


R1_{max}: Maximum resistance of device is measured one hours post reflow at 25°C.

Noted: All electrical function test is conducted after PCB mounted.


3、Thermal Derating

K0805L020/24AR	Maximum ambient operating temperature								
	-40℃	-20℃	0℃	25℃	40℃	50℃	60℃	70℃	85℃
Hold Current(A)	0.28	0.26	0.23	0.20	0.17	0.14	0.12	0.10	0.07
Trip Current(A)	0.70	0.65	0.59	0.50	0.44	0.36	0.32	0.27	0.19

4、Solder Reflow Recommendations



Recommended Pad Layout(mm)



Notes: If reflow temperatures exceed the recommended profile, devices may not meet the performance requirements.

5、Package Information

Packing quantity: 3500PCS/Reel

Note: Reel packaging per EIA-481-1 standard