


Features

- 400 watts Peak Pulse Power (10/1000 μ s)
- Unidirectional and Bidirectional Protection
- Fast Response Time : Typically < 1ns
- Excellent Clamping Capability
- Built-in Strain relief
- Low inductance
- Low profile package
- IEC 61000-4-2 (ESD) $\pm$ 30kV(air), $\pm$ 30kV(contact)
- MSL: Level 1



Mechanical Characteristics

- SOD-123FL package
- Matte tin lead - free plated
- Marking: Marking Code
- RoHS Compliant

Applications

- I/O Interfaces
- Power lines
- Telecommunication
- Industrial Electronics
- Consumer Electronics


Absolute Maximum Rating			
Rating	Symbol	Value	Units
Peak Pulse Power ($t_p = 10/1000\mu s$) (see Note1&2)	P_{PPM}	400	Watts
Peak pulse current (10/1000 μ s) (see Note2)	I_{PPM}	See Electrical Characteristics	A
Peak Forward surge current (see Note3)	I_{FSM}	20	A
Power Dissipation on infinite heat sink $T_L = 50^\circ C$ (Fig4)	P_D	1.0	W
Operating Junction Temperature range	T_J	-55 to + 150	$^\circ C$

Note1: Peak Pulse Power Rating as Pulse Width ,per Fig1.


Note2: Peak Pulse Power or Current Derated above $T_A=25^\circ C$ Per Fig. 2 and Non-Repetitive Current Pulse,Per Fig.3.

Note3: 8.3ms Single Half Sine Wave or Equivalent Square Wave unidirectional device only.

Pin Configuration



Unidirectional



Bidirectional

Electrical Characteristics

Part Number		Reverse Stand off Voltage V_{RWM} (Volts)	Breakdown Voltage $V_{BR@I_T}$ (Volts)		Test Current I_T (mA)	Maximum Clamping Voltage $V_C@I_{PP}$ (Volts)	Maximum Peak Pulse Current I_{PP} (Amps)	Maximum Reverse Leakage $I_R@V_{RWM}$ (μA)
UNI- POLAR	BI- POLAR		MIN	MAX				
SM4F5.0A	SM4F5.0CA	5.0	6.4	7.0	10	9.2	43.5	400
SM4F6.0A	SM4F6.0CA	6.0	6.67	7.37	10	10.3	38.8	400
SM4F6.5A	SM4F6.5CA	6.5	7.22	7.98	10	11.2	35.7	250
SM4F7.0A	SM4F7.0CA	7.0	7.78	8.6	10	12	33.3	100
SM4F7.5A	SM4F7.5CA	7.5	8.33	9.21	1	12.9	31.0	50
SM4F8.0A	SM4F8.0CA	8.0	8.89	9.83	1	13.6	29.4	25
SM4F8.5A	SM4F8.5CA	8.5	9.44	10.4	1	14.4	27.8	10
SM4F9.0A	SM4F9.0CA	9.0	10.0	11.1	1	15.4	26.0	5
SM4F10A	SM4F10CA	10	11.1	12.3	1	17	23.5	2.5
SM4F11A	SM4F11CA	11	12.2	13.5	1	18.2	22.0	2.5
SM4F12A	SM4F12CA	12	13.3	14.7	1	19.9	20.1	2.5
SM4F13A	SM4F13CA	13	14.4	15.9	1	21.5	18.6	1
SM4F14A	SM4F14CA	14	15.6	17.2	1	23.2	17.2	1
SM4F15A	SM4F15CA	15	16.7	18.5	1	24.4	16.4	1
SM4F16A	SM4F16CA	16	17.8	19.7	1	26	15.4	1
SM4F17A	SM4F17CA	17	18.9	20.9	1	27.6	14.5	1
SM4F18A	SM4F18CA	18	20.0	22.1	1	29.2	13.7	1
SM4F20A	SM4F20CA	20	22.2	24.5	1	32.4	12.3	1
SM4F22A	SM4F22CA	22	24.4	26.9	1	35.5	11.3	1
SM4F24A	SM4F24CA	24	26.7	29.5	1	38.9	10.3	1
SM4F26A	SM4F26CA	26	28.9	31.9	1	42.1	9.5	1
SM4F28A	SM4F28CA	28	31.1	34.4	1	45.4	8.8	1
SM4F30A	SM4F30CA	30	33.3	36.8	1	48.4	8.3	1
SM4F33A	SM4F33CA	33	36.7	40.6	1	53.3	7.5	1
SM4F36A	SM4F36CA	36	40.0	44.2	1	58.1	6.9	1
SM4F40A	SM4F40CA	40	44.4	49.1	1	64.5	6.2	1
SM4F43A	SM4F43CA	43	47.8	52.8	1	69.4	5.8	1
SM4F45A	SM4F45CA	45	50.0	55.3	1	72.7	5.5	1
SM4F48A	SM4F48CA	48	53.3	58.9	1	77.4	5.2	1
SM4F51A	SM4F51CA	51	56.7	62.7	1	82.4	4.9	1
SM4F54A	SM4F54CA	54	60.0	66.3	1	87.1	4.6	1
SM4F58A	SM4F58CA	58	64.4	71.2	1	93.6	4.3	1

Typical Characteristics

Figure 1: Peak Pulse Power Rating Curve




Figure 2: Pulse Derating Curve




Figure 3: Pulse Waveform




Figure 4: Steady State Power Dissipation Derating Curve






Figure 5: Maximum Non-Repetitive Forward Surge Current Only Unidirectional



Note: The above typical parameters or typical characteristics are only indicative and do not make specific guarantees. If detailed values are required, additional communication and provision are required.


Soldering Parameters

Reflow Condition		
Pre-Heat	Temperature min ($T_{S(min)}$)	150°C
	Temperature max ($T_{S(max)}$)	200°C
	Time (min to max) (t_s)	60-190 s
Average ramp up rate (Liquidus Temp) (T_L) to peak		3°C/s max
$T_{S(max)}$ to T_L - Ramp-up Rate		3°C/s max
Reflow	Temperature (T_L) (Liquidus)	217°C
	Temperature (t_L)	60-150 s
Peak Temperature (T_P)		260 ^{+0/-5} °C
Time within actual peak Temperature (t_p)		20-40 s
Ramp-down Rate		5°C/s max
Time 25°C to peak Temperature (T_P)		8 minutes max
Do not exceed		260°C




Outline Drawing – SOD-123FL

Ref. (mm)	Millimeters	
	Min.	Max.
A	2.50	2.95
B	3.40	3.95
C	0.70	1.10
D	1.50	1.90
E	0.45	0.95
F	0.05	0.26
G	0.90	1.35



Recommended Solder Pad Layout



Dimensions in mm