





ROHS



RECOMMENDED PCB LAYOUT
TOP VIEW TOLERANCE: ± 0.05




SCHEMATIC



PIN	$\phi 2.1$	$\phi 2.5$
APPD	✓	

技术要求

- 1、插入力: 3~30N(0.3~3.0kgf)
- 2、拔出力: 3~30N(0.3~3.0kgf)
- 3、接触电阻: $\leq 50\text{m}\Omega$
- 4、绝缘电阻: $>100\text{M}\Omega$ DC 500V
- 5、耐电压: AC 500V 1min无飞弧及击穿
- 6、寿命: 5000 10~20次/min
- 7、额定负载: DC 20V 7A
- 8、适用温度范围: $-25\sim 85^{\circ}\text{C}$
- 9、推荐使用插头:



4	JQ-DC-0005U-04	3号脚	1PCS	C5191磷铜=0.25	镀锡	环保
3	JQ-DC-0005U-03	2号脚	1PCS	C5191磷铜=0.25	镀锡	环保
2	JQ-DC-0005U-02	1号脚	1PCS	C5210黄铜=0.40	镀锡	环保
1	JQ-DC-0005U-01	塑料座	1PCS	PPA	黑色	环保
序号	零件图代号	名称	数量	材料	镀层/颜色	备注
深圳市首韩科技有限公司				1. 线性 X ± 0.15 X.X ± 0.10 X.XX ± 0.05	2. 角度 XX° $\pm 3^{\circ}$ X° $\pm 2^{\circ}$ X.X° $\pm 1^{\circ}$	
绘制	李春风	日期	2018.6.6	品名	DC POWER JACK	
审核	钟华华	日期	2018.6.6	型号	DC005U-2.0-T	
批准	罗孝金	日期	2018.6.6	页码	1F1	A4



深圳市首韩科技有限公司

SHENZHEN SHOUHAN TECHNOLOGY CO., LTD

Tel: 0755-27597601 Fax: 0755-27597491

承 认 书

SPECIFICATION FOR APPROVAL

产 品 编 码

Material code:

产品名称 Project:

DC座

规格型号 Part No:

DC005U-2.0-T

贵公司承认印 Approval signatures

料 号/Part No.	签 章/Signatures

日期 Date:

拟制/Drawn	李春风	
审核/Check	钟华华	
批准/Approved	罗孝金	



深圳市首韩科技有限公司

品名 (NAME): DC座

型号 (MODEL): DC005U-2.0-T

1. 溫度5~35℃, 湿度45~85%標準狀態下測試。

In normal fettle to test. Temperature 5~35℃ and humidity 45~85%

2. 溫度-30~70℃環保內使用。

In entironment of remperature -30~70℃

ITEM 專案

TEST CONDITION 測試條件

SPECIFICICAION 規格

3. ELECTRONICAL RESISTAN 電氣性能

3.1	CONTACT RESISANCE 接觸阻抗	Being measured at 1KHZsmall current connect resistance meter.在1KHZ小電流下測量。	0.05欧姆以下
3.2	INSULATION RESISTANCE 絕緣阻抗	Measurements shall be made following application of DC500V poten rial across terminals and across terminals and frame for 1 minute.在端子之間和端子與殼之間加DC500V條件下，持續1分鐘測量。	100M min 100兆歐以上。
3.3	WITHSTAND VOLTAGE 耐電壓	AC500V(50HZ or 60HZ) shall be applied across terminals and across terminals and frame for one minute.在端子之間和端子與殼之間加AC500V條件下，持續1分鐘測量。	There shall be no breakdown 無擊穿現象。

4. MECHANICAL CHARACTERISTICS 機械性能

4.1	INSERION AND WITHDRAW 插拔力	Being measure at across spring piece and across matching plug for ergo meter. 用測力計在插頭與彈片之間進行測試	Insertion and extraction force 3-30N, 插拔力3-30N
4.2	TERMINAL STRENGTH 端子強度	A static force of 500gf being applied in one directionon the top of terminal for 1 minute.一個500克之靜負荷施加於端子頂部的一個方向持續1分鐘。	There shall be no sign of damage mechanical and electrically. 無任何迹象顯示機械及電器性能之損壞。



5. DURABILTY 耐 久 性

5.1	SOLDERING TEST 可焊性試驗	The top of terminals shall be dipped 2mm in the loder bath at a temperature of 230: 5°C for 3sec. 端子頂部被浸入焊池2mm深，溫度230±5°C時間3秒	A new un form coating of shall cover above 75 % of the surface being Immersed. 浸入的部分75%以上表面將被錫覆蓋。
5.2	LIFE TEST 壽命試驗	5000 cycles of operation at rate of 20-30 cycles per minture with unloading. 無負載條件下，每分鐘20—30次的速度操作5000次。	(1) Contact resistance.40mΩ max 接觸阻抗40毫歐以下 (2) Drive fore 30 inital value 動作力變化範圍初始值30 (3) ITEM專案—3.2 (4) ITEM專案—3.3 (5) INEM—4.2
5.3	HEAT TEST 耐熱試驗	80: 2°C for 48 hours after test keep in normal condition for 30minutes. 在80±2°C環境中放48小時，再放在正常環境中30分鐘後進行測試。	(1) Contact resistance 50mΩ max.接觸電阻50毫歐以下
5.4	HUMIDITY TEST 耐濕試驗	The condition of temperature 40±2-°C and humidity 90-95 %for 48 hours after test keep in normal condition for 30 min.在40±2-°C 90—95 % Rh環境中放48小時，再放在正常環境中30分鐘後進行測試。	(2) Insulation resistance 100MΩ min.絕緣電阻100M歐以上 (3) There shall be no sign of damage mechanically and electrically.無任何迹象顯示機械及電器性能之損壞。
5.5	COLD TEST 耐冷試驗	At—30±2-°C for 48 hours,after test keep in normal condition for 30 min.在—30 ± 2-°C環境中放48小時，再置於正常環境中30分鐘後進行測試。	