

MNTC0402X104J4150HTB

Chip Temp. Sensing NTC Thermistor

FEATURES

- SMD type suitable for high density mounting
- Series of B constant for various applications
- Excellent solder ability
- Operate temperature range $-40^{\circ}\text{C} \sim +125^{\circ}\text{C}$.
- RoHS compliant

APPLICATIONS

- Telecommunication equipments such as cellular phone, automobile phone, etc.
- Office automation such as printer, facsimile, word processor, etc.
- Battery, CPU temperature protection.



PRODUCT IDENTIFICATION

MNTC 0402 X 104 J 4150 H T B

1 2 3 4 5 6 7 8 9

- 1:Product Series: Chip Temp. Sensing NTC Thermistor
- 2:Dimensions:0402[1005]:1.0×0.5×0.5
- 3:Delimiter:X
- 4:Nominal Zero-Power Resistance at 25°C : 104: 100k Ω
- 5:Tolerance of Resistance:F $\pm 1\%$,G $\pm 2\%$,H $\pm 3\%$,J $\pm 5\%$
- 6:B Constant:4150:4150K
- 7:Tolerance of B Constant:F $\pm 1\%$, H $\pm 3\%$
- 8: Packing:Tape Carrier Package
- 9:B constant calculation method:A 25°C & 85°C ;B: 25°C & 50°C

Dimensions: [mm]



Recommended PCB pattern for reflow soldering

unit: inch[mm]

Type	L	W	T	a	A	B	C
0402 [1005]	0.039±0.006 [1.0±0.15]	0.020±0.006 [0.5±0.15]	0.020±0.006 [0.5±0.15]	0.010±0.004 [0.25±0.1]	[0.45-0.55]	[0.4-0.5]	[0.45-0.55]

Electrical Characteristics List

Part No	Resistance (25℃) (kΩ)	B Constant (25/50℃) (K)	B Constant (25/85℃) (K)	Permissible Operating Current (25℃) (mA)	Dissipation Factor (mW/℃)	Thermal Time Constant (s)	Rated Electric Power(25℃) (mW)	Operating ambient temperature (℃)
MNTC0402X104J4150HTB	100±5%	4150±3%	4209 ref.	0.10	1.0	<3	100	-40~+125

Test and Measurement Procedures

• Test Conditions

Unless otherwise specified, the standard atmospheric conditions for measurement/test as:

- a. Ambient Temperature: $20 \pm 15^{\circ}\text{C}$
- b. Relative Humidity: $65 \pm 20\%$
- c. Air Pressure: 86kPa to 106kPa

If any doubt on the results, measurements/tests should be made within the following limits:


- a. Ambient Temperature: $25 \pm 2^{\circ}\text{C}$
- b. Relative Humidity: $65 \pm 5\%$
- c. Air Pressure: 86kPa to 106kPa

• Inspection Equipment

Visual Examination: 20×magnifier

Resistance value test: Thermistor resistance tester

Electrical Test

No.	Items	Test Methods and Remarks
1	Nominal Zero-Power Resistance at 25°C (R25)	Ambient temperature: $25 \pm 0.05^{\circ}\text{C}$ Measuring electric power: $\leq 0.1\text{mW}$
2	Nominal B Constant	Measure the resistance at the ambient temperature of $25 \pm 0.05^{\circ}\text{C}$, $50 \pm 0.05^{\circ}\text{C}$ or $85 \pm 0.05^{\circ}\text{C}$. $B(25-50^{\circ}\text{C}) = \frac{\ln R_{25} - \ln R_{50}}{1/T_{25} - 1/T_{50}} \quad B(25-85^{\circ}\text{C}) = \frac{\ln R_{25} - \ln R_{85}}{1/T_{25} - 1/T_{85}}$ T: (K) Absolute temperature (K)
3	Thermal Time Constant	The total time for the temperature of the thermistor to change by 63.2% of the difference from ambient temperature $T_0 (^{\circ}\text{C})$ to $T_1 (^{\circ}\text{C})$ by the drastic change of the power applied to thermistor from Non-zero Power to Zero-Power state, normally expressed in second(S). 

Reliability Test

		Test Methods and Remarks	Requirements
--	--	--------------------------	--------------

www.metal-lions.com


Vibration	IEC 60068-2-80	① Solder the chip to the testing jig (glass epoxy board shown in the left) using eutectic solder. ② The chip shall be subjected to a simple harmonic motion having total amplitude of 1.5mm, the frequency being varied uniformly between the approximate limits of 10 and 55 Hz. ③ The frequency ranges from 10 to 55 Hz and return to 10 Hz shall be traversed in approximately 1 minute. This motion shall be applied for a period of 2 hours in each 3mutually perpendicular directions (total of 6 hours).	No visible damage. 铜粒 Chip pad 阻焊膜 Solder mask 环氧玻璃布板Glass Epoxy Board 															
Dropping	IEC 60068-2-32	Drop a chip 10 times on a concrete floor from a height of 1 meter.	No visible damage.															
Solderability	IEC 60068-2-58	① Solder temperature: 245±5 ℃. ② Duration: 3±0.3s. ③ Solder: 96.5Sn/3.0Ag/0.5Cu. ④ Flux: （重量比）25%松香和 75%酒精25% Resin and 75% ethanol in weight.	① No visible damage. ② Wetting shall exceed 95% coverage															
Resistance to Soldering Heat	IEC 60068-2-58	① Solder temperature: 260±5 ℃ . ② Duration: 10±1s. ③ Solder: 96.5Sn/3.0Ag/0.5Cu. ④ Flux: （重量比）25%松香和 75%酒精25% Resin and 75% ethanol in weight. ⑤ The chip shall be stabilized at normal condition for 1~2 hours before measuring.	① No visible damage. ② ΔR25/R25 ≤2% ③ ΔB/B ≤1%															
Temperature cycling	IEC 60068-2-14	① <table><tr><th>Step</th><th>Temperature</th><th>Time</th></tr><tr><td>1</td><td>-40±5℃</td><td>30±3min</td></tr><tr><td>2</td><td>25±2℃</td><td>5±3min</td></tr><tr><td>3</td><td>125±2℃</td><td>30±3min</td></tr><tr><td>4</td><td>25±2℃</td><td>5±3min</td></tr></table> ② The chip shall be stabilized at normal condition for 1~2 hours before measuring.	Step	Temperature	Time	1	-40±5℃	30±3min	2	25±2℃	5±3min	3	125±2℃	30±3min	4	25±2℃	5±3min	① No visible damage. ② ΔR25/R25 ≤2% ③ ΔB/B ≤1%
Step	Temperature	Time																
1	-40±5℃	30±3min																
2	25±2℃	5±3min																
3	125±2℃	30±3min																
4	25±2℃	5±3min																
Resistance to dry heat	IEC 60068-2-2	① 125±5℃ in air, for 1000±24 hours without loading. ② The chip shall be stabilized at normal condition for 1~2 hours before measuring.	① No visible damage. ② ΔR25/R25 ≤2% ③ ΔB/B ≤1%															

Resistance to cold	IEC 60068-2-1	① $-40\pm 3^{\circ}\text{C}$ in air, for 1000 ± 24 hours without loading. ② The chip shall be stabilized at normal condition for 1~2 hours before measuring.	① No visible damage. ② $ \Delta R_{25}/R_{25} \leq 2\%$ ③ $ \Delta B/B \leq 1\%$
Resistance to damp heat	IEC 60068-2-78	① $40\pm 2^{\circ}\text{C}$, 90~95%RH in air, for 1000 ± 24 hours without loading. ② The chip shall be stabilized at normal condition for 1~2 hours before measuring.	① No visible damage. ② $ \Delta R_{25}/R_{25} \leq 2\%$ ③ $ \Delta B/B \leq 1\%$
Resistance to high temperature load	IEC 60539-1 5.25.4	① $85\pm 2^{\circ}\text{C}$ in air with permissive operating current for 1000 ± 48 hours ② The chip shall be stabilized at normal condition for 1~2 hours before measuring.	① No visible damage. ② $ \Delta R_{25}/R_{25} \leq 2\%$ ③ $ \Delta B/B \leq 1\%$


Taping

Type	0402
Tape thickness(mm)	0.5 ± 0.15
Tape material	Paper Tape
Quantity per Reel	10K


Taping Drawings



Paper Tape Dimensions



Reel Dimensions Unit: mm)



Storage

- **Storage Conditions**
 - a. Storage Temperature: -10℃～40℃
 - b. Relative Humidity: ≤75%RH
 - c. Keep away from corrosive atmosphere and sunlight.
- **Period of Storage: 6 Months**


Notes & Warnings

- The MNTC series thermistors shall not be operated and stored under the following environmental condition:
 - (1) Corrosive or deoxidized atmospheres
(such as chlorine, sulfured hydrogen, ammonia, sulfuric acid, nitric oxide and so on)
 - (2) Volatile or inflammable atmospheres
 - (3) Dusty condition
 - (4) Excessively high or low pressure condition
 - (5) Humid site
 - (6) Places with brine, oil, chemical liquid or organic solvent
 - (7) Intense vibration
 - (8) Places with analogously deleterious conditions
- The ceramic body of the MNTC series thermistors is fragile, no excessive pressure or impact shall be exerted on it.
- The MNTC series thermistors shall not be operated beyond the specified "Operating Temperature Range" in the catalog.

Recommended Soldering Technologies


Re-flowing Profile

- 1~2°C/sec. Ramp
- Pre-heating: 150~170°C/90±30 sec.
- Time above 240°C: 20~40 sec.
- Peak temperature: 260°C Max./10 sec.
- Solder paste: 96.5Sn/3.0Ag/0.5Cu
- Max.2 times for re-flowing



Iron Soldering Profile

- Iron soldering power: Max.20W
- Pre-heating: 150°C/60sec.
- Soldering Tip temperature: 280°C Max.
- Soldering time: 3 sec Max.
- Solder paste: 96.5Sn/3.0Ag/0.5Cu
- Max.1 times for iron soldering



[Note: Take care not to apply the tip of the soldering iron to the terminal electrodes.]