

74LS08

DATASHEET

Specification Revision History:

Version	Date	Description
V1.0	2019/11	New
V1.1	2021/07	Modify Ordering Information
V1.2	2025/02	Modify Ordering Information
V1.3	2025/03	Add application precautions and overall typesetting.

Description

The 74LS08 contains four independent 2-input AND gates, perform the Boolean function $Y = \overline{\overline{A} \cdot \overline{B}}$ or $Y = A + B$ in positive logic.

FEATURES

- Operation Voltage Range: 2~6V
- Low Quiescent Current: $I_{CC} = 2\mu A$ (Max)
- High Speed: $t_{PD} = 8ns$ (Typ)
- Low Input Current: 100nA (Max)
- ESD protection:
 - HBM: ANSI/ESDA/JEDEC JS-001 2023 exceeds 1000V
 - CDM: ANSI/ESDA/JEDEC JS-002 2022 exceeds 2000V
- Latch-up performance $\leq 250mA$
- Package Option: DIP-14, SOP-14 and TSSOP-14

The appearance of the product




SOP-14

Ordering Information

Product Model	Package Type	Marking	Packing	Packing Qty
SN74LS08DS	SOP-14	74LS08 3B3	REEL	4000PCS/REEL

PIN CONFIGURATION



FUNCTION TABLE(Each Gate)

INPUT(A)	OUTPUT(Y)
H	H
H	L
L	H
L	L

LOGIC DIAGRAM(positive logic)



ABSOLUTE MAXIMUM RATING ($T_A = 25^{\circ}\text{C}$, unless otherwise specified) (Note 2)

PARAMETER	SYMBOL	RATINGS	UNIT
Supply Voltage	V_{CC}	-0.5 ~ 7	V
Input Clamp Current	I_{IK}	± 20	mA
Output Clamp Current	I_{OK}	± 20	mA
Output Current	I_{OUT}	± 25	mA
VCC or GND Current	I_{CC}	± 50	mA
Storage Temperature	T_{STG}	-65 ~ +150	$^{\circ}\text{C}$

Note: Absolute maximum ratings are those values beyond which the device could be permanently damaged. Absolute maximum ratings are stress ratings only and functional device operation is not implied.

RECOMMENDED OPERATING COMDITIONS

PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNIT
Supply Voltage	V_{CC}	-	2	-	6	V
Input Voltage	V_{IN}	-	0	-	V_{CC}	V
Output Voltage	V_{OUT}	-	0	-	V_{CC}	V
Input Transition Rise or Fall Rate	t_R, t_F	$V_{CC}=2V$	-	-	1000	ns
		$V_{CC}=4.5V$	-	-	500	
		$V_{CC}=6V$	-	-	400	
Operating Temperature	T_A	-	-40	-	+125	°C

THERMAL DATA

PARAMETER		SYMBOL	RATINGS	UNIT
Junction to Ambient	DIP-14	θ_{JA}	100	°C/W
	SOP-14		125	°C/W
	TSSOP-14		150	°C/W

STATIC CHARACTERISTICS ($T_A=25^\circ\text{C}$, unless otherwise specified)


PARAMETER	SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	UNIT
High-Level Input Voltage	V_{IH}	$V_{CC}=2V$	1.5	-	-	V
		$V_{CC}=4.5V$	3.15	-	-	V
		$V_{CC}=6V$	4.2	-	-	V
Low-Level Input Voltage	V_{IL}	$V_{CC}=2V$	-	-	0.5	V
		$V_{CC}=4.5V$	-	-	1.35	V
		$V_{CC}=6V$	-	-	1.8	V
High-Level Output Voltage	V_{OH}	$V_{CC}=2V, I_{OH}=-20\mu A$	1.9	1.998	-	V
		$V_{CC}=4.5V, I_{OH}=-20\mu A$	4.4	4.499	-	V
		$V_{CC}=6V, I_{OH}=-20\mu A$	5.9	5.999	-	V
		$V_{CC}=4.5V, I_{OH}=-4mA$	3.98	4.32	-	V
		$V_{CC}=6V, I_{OH}=-5.2mA$	5.48	5.81	-	V
Low-Level Output Voltage	V_{OL}	$V_{CC}=2V, I_{OL}=20\mu A$	-	0.002	0.1	V
		$V_{CC}=4.5V, I_{OL}=20\mu A$	-	0.001	0.1	V
		$V_{CC}=6V, I_{OL}=20\mu A$	-	0.001	0.1	V
		$V_{CC}=4.5V, I_{OL}=4mA$	-	0.15	0.26	V
		$V_{CC}=6V, I_{OL}=5.2mA$	-	0.16	0.26	V
Input Leakage Current	$I_{I(LEAK)}$	$V_{CC}=6V, V_{IN}=V_{CC}$ or GND	-	± 0.1	± 100	nA
Quiescent Supply Current	I_Q	$V_{CC}=6V, V_{IN}=V_{CC}$ or GND $I_{OUT}=0$	-	-	8	μA
Input Capacitance	C_{IN}	$V_{CC}=2V$ to $6V$	-	3	10	pF

DYNAMIC CHARACTERISTICS ($T_A=25^\circ\text{C}$, Input: $t_R, t_F=6ns$, unless otherwise specified)


PARAMETER	SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	UNIT
Propagation delay from Input(A or B) to Output(Y)	t_{PLH}, t_{PHL}	$V_{CC}=2V, C_L=50pF$	-	25	90	ns
		$V_{CC}=4.5V, C_L=50pF$	-	9	18	ns
		$V_{CC}=6V, C_L=50pF$	-	7	15	ns
Output Transition Time	t_T	$V_{CC}=2V$	-	19	75	ns
		$V_{CC}=4.5V$	-	7	15	ns
		$V_{CC}=6V$	-	6	13	ns

OPERATING CHARACTERISTICS (TA=25°C, unless otherwise specified)

PARAMETER	SYMBOL	TEST CONDITION	RATINGS	UNIT
Power Dissipation Capacitance	C_{PD}	No Load	20	pF

TEST CIRCUIT AND WAVEFORMS



Note: C_L includes probe and jig capacitance.



Outline Dimensions

SOP-14

Unit : mm



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	1.350	1.750	0.053	0.069
A1	0.100	0.250	0.004	0.010
A2	1.350	1.550	0.053	0.061
b	0.330	0.510	0.013	0.020
c	0.170	0.250	0.007	0.010
D	8.360	8.760	0.329	0.345
E	3.800	4.000	0.150	0.157
E1	5.800	6.200	0.228	0.244
e	1.270 (BSC)		0.050 (BSC)	
L	0.400	1.270	0.016	0.050
θ	0 °	8 °	0 °	8 °

Important Notice

- Green Micro chip reserves the right to change products and documents without notice. Customers should obtain and verify the completeness of the latest technical information before placing orders. Meanwhile, Green Micro chip shall not assume any responsibility or obligation for non-officially revised documents.
- Any parameters in the entire product specification are for reference only, and actual application testing shall prevail. When customers use the products for system design, they must comply with safety regulations and independently assume the following responsibilities: selecting suitable Green Micro chip products according to application requirements; completing design verification and full-link testing of the application; and ensuring that the application complies with safety regulations or other requirements of the target market. Customers shall bear all personal or property losses caused by design defects or illegal operations, which shall have no relation to Green Micro chip.
- Green Micro chip products are prohibited from being used in scenarios such as life support, military equipment, and key aerospace applications. All accidents and legal liabilities arising from out-of-scope use shall be borne by the user, and Green Micro chip shall not be held responsible.
- All technical resources of Green Micro chip (including data sheets and reference designs) are provided "as is", without guarantee of no defects or universality, and without any express or implied warranties. The documents are only authorized for product development and research described in this document. Unauthorized use of intellectual property, public reproduction, and reverse engineering are strictly prohibited. All claims and losses caused by illegal use shall be borne by the user, and Green Micro chip shall not be liable.