





RoHS



NOTE:

1. Rating: 24V 25mA DC
2. Insulation Resistance: $\geq 100 \text{ M}\Omega$
3. Withstand voltage: AC 500V 1Minute
4. Operating Force Range: 1000gf Max
5. Mechanical Life: 3,000 Cycles

(F)	Dust film		1	Polyimide tape	
(E)	Terminal		20	Phosphor bronze	Gold plating
(D)	Contact spring		10	Phosphor bronze	Gold plating
(C)	Handle		10	PA46	White
(B)	Cover		1	PPS	Black
(A)	Base		1	PPS	Black
NO.	Name	Number	Qty	Materil	Remarks

YUANDI® Yuandi Electronics Co., Ltd

design	date	name	DIP SWITCH
Review	date	model	TP-10
Approved	date		

Drawing number: Proportion 1:1 unit mm gage number A4

modify Review Approved

angle	$\pm 2^\circ$
10~30	± 0.30
5~10	± 0.20
~ 5	± 0.10

Tolerance not specified