






RoHS



NOTE:
1.Rating: 24V 25mA DC
2.Insulation Resistance: $\geq 100 \text{ M}\Omega$
3.Withstand voltage: AC 500V 1Minute
4.Operating Force Range: 1000gf Max
5.Mechanical Life: 3,000 Cycles

(F)	Dust film		1	Polyimide tape	
(E)	Terminal		4	Phosphor bronze	Gold plating
(D)	Contact spring		2	Phosphor bronze	Gold plating
(C)	Handle		2	PA46	White
(B)	Cover		1	PPS	Black
(A)	Base		1	PPS	Black
NO.	Name	Number	Qty	Materil	Remarks



Zhongdi Electronic Technology Co., Ltd

design	date	name	DIP SWITCH
Review	date	model	DSHP-02
Approved	date		

Drawing number:

modify	Review	Approved	Tolerance not specified	Proportion	1:1	unit	mm	gap	number	A4
--------	--------	----------	-------------------------	------------	-----	------	----	-----	--------	----