


Wire Wound Type Common Mode Filter

- 1.High common mode impedance at high frequency cause excellent noise suppression performance.
- 2.CWCM3216F series realizes small size and low profile. 3.2x1.6x2.0 mm.
- 3.100% Lead(Pb) & Halogen-Free and RoHS compliant.
- 4.Operating temperature-40~+105℃




Part Number	Common mode Impedance (Ω)	Test Frequency (MHz)	DC Resistance (Ω) max.	Rated Current (mA)max.	Rated Volt. (Vdc)max.	Withstand Volt. (Vdc) max.	IR (Ω) min.
CWCM3216F-2-600T02	60±25%	100	1.10	200	50	125	10M
CWCM3216F-2-900T04	90±25%	100	0.30	400	50	125	10M
CWCM3216F-2-121T03	120±25%	100	0.30	350	50	125	10M
CWCM3216F-2-161T03	160±25%	100	0.40	350	50	125	10M
CWCM3216F-2-221T03	220±25%	100	0.45	300	50	125	10M
CWCM3216F-2-261T03	260±25%	100	0.50	300	50	125	10M
CWCM3216F-2-361T03	360±25%	100	0.60	300	50	125	10M
CWCM3216F-2-601T03	600±25%	100	0.80	300	50	125	10M
CWCM3216F-2-102T02	1000±25%	100	1.00	200	50	125	10M
CWCM3216F-2-222T02	2200±25%	100	1.20	200	50	125	10M

MECHANICAL




SCHEMATICS




SOLDERING IRON











SUGGEST LAYOUT




Dimension: mm



IMPEDEANCE FREQUENCY






TAPING AND PACKING



IND1752-J-E

Quantity (pcs):
2000 PCS PER REEL
5 REELS PER CARTON
10000PCS PER CARTON

Reel



Dimensions in mm