

CMP330N15/CMB330N15/CMI330N15/CMF330N15

150V, 29mΩ typ., 60A N-Channel MOSFET

General Description

The 330N15 uses advanced SGT technology to provide excellent $R_{DS(ON)}$. This device is ideal for boost converters and synchronous rectifiers for consumer, telecom, industrial power supplies and LED backlighting.

Features

- Low On-Resistance
- 100% avalanche tested
- RoHS Compliant


Product Summary

BVDSS	$R_{DS(on)}$ max.	ID
150V	33mΩ	60A

Applications

- High Frequency Switching and Synchronous Rectification

TO-220/263/262/220F Pin Configuration



Absolute Maximum Ratings

Symbol	Parameter	220/263/262	220F	Units
V_{DS}	Drain-Source Voltage	150		V
V_{GS}	Gate-Source Voltage	±20		V
$I_D@T_C=25^\circ\text{C}$	Continuous Drain Current	60	60*	A
$I_D@T_C=100^\circ\text{C}$	Continuous Drain Current	42	42*	A
I_{DM}	Pulsed Drain Current	240	240*	A
EAS	Single Pulse Avalanche Energy (Note 1)	162		mJ
$P_D@T_C=25^\circ\text{C}$	Total Power Dissipation	140	40	W
T_{STG}	Storage Temperature Range	-55 to 150		°C
T_J	Operating Junction Temperature Range	-55 to 150		°C

* Drain current limited by maximum junction temperature.

Thermal Data

Symbol	Parameter	220/263/262	220F	Unit
$R_{\theta JA}$	Thermal Resistance Junction-ambient Max.(Steady-State)	42	42	°C/W
$R_{\theta JC}$	Thermal Resistance Junction-case Max.	0.89	3.13	°C/W

CMP330N15/CMB330N15/CMI330N15/CMF330N15

150V, 29mΩ typ., 60A N-Channel MOSFET

Electrical Characteristics ($T_J=25^{\circ}\text{C}$, unless otherwise noted)

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
BV_{DSS}	Drain-Source Breakdown Voltage	$V_{GS}=0V$, $I_D=250\mu A$	150	---	---	V
$R_{DS(ON)}$	Static Drain-Source On-Resistance	$V_{GS}=10V$, $I_D=20A$	---	29	33	mΩ
$V_{GS(th)}$	Gate Threshold Voltage	$V_{GS}=V_{DS}$, $I_D=250\mu A$	2.0	---	4.0	V
I_{DSS}	Drain-Source Leakage Current	$V_{DS}=150V$, $V_{GS}=0V$	---	---	1	uA
I_{GSS}	Gate-Source Leakage Current	$V_{GS}=\pm 20V$, $V_{DS}=0V$	---	---	± 100	nA
g_{fs}	Forward Transconductance	$V_{DS}=15V$, $I_D=20A$	---	12	---	S
R_g	Gate Resistance	$V_{DS}=0V$, $V_{GS}=0V$, $f=1\text{MHz}$	---	1.5	---	Ω
Q_g	Total Gate Charge	$I_D=16A$	---	12	---	nC
Q_{gs}	Gate-Source Charge	$V_{DD}=75V$	---	5	---	
Q_{gd}	Gate-Drain Charge	$V_{GS}=0$ to $10V$	---	2	---	
$T_{d(on)}$	Turn-On Delay Time	$V_{DD}=75V$	---	9	---	ns
T_r	Rise Time	$V_{GS}=10V$	---	6	---	
$T_{d(off)}$	Turn-Off Delay Time	$R_G=1.6\Omega$	---	12	---	
T_f	Fall Time	$I_D=16A$	---	4	---	
C_{iss}	Input Capacitance	$V_{DS}=25V$, $V_{GS}=0V$, $f=1\text{MHz}$	---	750	---	pF
C_{oss}	Output Capacitance		---	500	---	
C_{rss}	Reverse Transfer Capacitance		---	35	---	

Diode Characteristics

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
I_S	Continuous Source Current	$V_G=V_D=0V$, Force Current	---	---	60	A
I_{SM}	Pulsed Source Current		---	---	240	A
V_{SD}	Diode Forward Voltage	$V_{GS}=0V$, $I_S=20A$, $T_J=25^{\circ}\text{C}$	---	0.90	1.2	V
t_{rr}	Reverse Recovery Time	$di/dt=100A/\mu s$	---	80	---	ns
Q_{rr}	Reverse Recovery Charge	$T_J=25^{\circ}\text{C}$, $I_F=12A$	---	144	---	nC

Note :







1.The EAS data shows Max. rating .The test condition is $V_{DS}=80V$, $V_{GS}=10V$, $L=1\text{mH}$, $I_{AS}=18A$.

This product has been designed and qualified for the consumer market.

Cmos assumes no liability for customers' product design or applications.

Cmos reserves the right to improve product design ,functions and reliability without notice.Please refer to the latest version of specification.

Typical Characteristics




CMP330N15/CMB330N15/CMI330N15/CMF330N15

150V, 29mΩ typ., 60A N-Channel MOSFET

Package Dimension

TO-220

Unit :mm



DIM	MILLIMETERS
A	10.0±0.3
A1	8.64±0.2
A2	1.15±0.1
A3	5.0±0.2
B	15.8±0.4
B1	13.2±0.3
C	4.56±0.1
C1	1.3±0.2
D	0.8±0.2
E	3.6±0.2
F	2.95±0.3
G	6.5±0.3
H	0.5±0.1
K	3.1±0.2
L	13.2±0.4
M	1.25±0.1
N	2.54±0.1
P	2.4±0.3
Q	9.0±0.3
T	W:0.35
DIA	⊙1.5 (deep 0.2)


CMP330N15/CMB330N15/CMI330N15/CMF330N15

150V, 29mΩ typ., 60A N-Channel MOSFET


Package Dimension

TO-263

Unit :mm



DIM	MILLIMETERS
A	9.8 ± 0.2
a	7.4 ± 0.4
B	4.5 ± 0.2
b1	1.3 ± 0.05
b2	2.4 ± 0.2
H	15.5 ± 0.3
h	1.54 ± 0.2
h1	10.5 ± 0.2
h2	9.2 ± 0.1
h3	1.54 ± 0.2
h4	2.7 ± 0.2
L	2.4 ± 0.2
1	1.3 ± 0.1
11	0.8 ± 0.1
12	1.3 ± 0.1
13	0.5 ± 0.1
N	2.54 ± 0.1
R	$0.5R \pm 0.05$

Package Dimension
TO-262
Unit :mm


DIM	MILLIMETERS
A	9.98 ± 0.2
a	7.4 ± 0.4
B	4.5 ± 0.2
b1	1.3 ± 0.05
b2	2.4 ± 0.2
H	23.9 ± 0.3
h	3.1 ± 0.2
h1	9.16 ± 0.2
h2	13.2 ± 0.2
L	0.5 ± 0.1
l1	1.3 ± 0.1
l2	0.8 ± 0.1
N	2.45 ± 0.1


CMP330N15/CMB330N15/CMI330N15/CMF330N15

150V, 29mΩ typ., 60A N-Channel MOSFET

Package Dimension

TO-220F

Unit :mm



DIM	MILLIMETERS
A	10.16 ± 0.3
A1	7.00 ± 0.1
A2	3.3 ± 0.2
A3	9.5 ± 0.2
B1	15.87 ± 0.3
B2	4.7 ± 0.2
B3	6.68 ± 0.4
C	3.3 ± 0.2
C1	12.57 ± 0.3
C2	10.02 ± 0.5
D	2.54 ± 0.05
D1	1.28 ± 0.2
D2	0.8 ± 0.1
K	3.1 ± 0.3
E1	2.54 ± 0.1
E3	0.5 ± 0.1
E4	2.76 ± 0.2
DIA	$\varnothing 1.5$ (deep 0.2)