

						RoHS																																																		
DIMA±0.20 3.96±0.10 1P 2P • • • • • ① DIMB±0.25 14.0±0.20 1.14±0.05 ② DIMA±0.10 3.96±0.05 ø1.70±0.05 适用线路板 (PCB LAYOUT) 8.65±0.25 4.80±0.20 9.40±0.25 3.20±0.20 6.70±0.20 3.60±0.20 8.00±0.20 技术指标(Technical Index): 1. 温度范围(Temperature range): -25° C~+85° C. 2. 额定电压(Rated voltage): 250V, AC, DC. 3. 额定电流(Rated current): 7.0A AC, DC. 4. 接触电阻(Contact resistance): ≤20mΩ . 5. 耐压值(Withstanding voltage): 1500V AC/minute. 6. 绝缘电阻(Insulation resistance): ≥1000MΩ. <table><tr><th>CKT</th><th>A</th><th>B</th></tr><tr><td>2</td><td>3.96</td><td>7.92</td></tr><tr><td>3</td><td>7.92</td><td>11.88</td></tr><tr><td>4</td><td>11.88</td><td>15.84</td></tr><tr><td>5</td><td>15.84</td><td>19.80</td></tr><tr><td>6</td><td>19.80</td><td>23.76</td></tr><tr><td>7</td><td>23.76</td><td>27.72</td></tr><tr><td>8</td><td>27.72</td><td>31.68</td></tr><tr><td>9</td><td>31.68</td><td>35.64</td></tr><tr><td>10</td><td>35.64</td><td>39.60</td></tr><tr><td>11</td><td>39.60</td><td>43.56</td></tr><tr><td>12</td><td>43.56</td><td>47.52</td></tr><tr><td>13</td><td>47.52</td><td>51.48</td></tr><tr><td>14</td><td>51.48</td><td>55.44</td></tr><tr><td>15</td><td>55.44</td><td>59.40</td></tr><tr><td>16</td><td>59.40</td><td>63.36</td></tr></table> OPERATION X.X ±0.30 X.XX ±0.20 X.XXX ±0.10 Angle ±3° DIM TOL DRAW CHECK APPROVE SCALE FIT UNIT mm SHEET A4 PROJ. 深圳市连盛精密连接器有限公司 PART NO. 1130500038 TITLE: VH-NA REV 1 DATE MODIFICATION DESCRIPTION CHANGE 2 3 4 5 6 7 8 9									CKT	A	B	2	3.96	7.92	3	7.92	11.88	4	11.88	15.84	5	15.84	19.80	6	19.80	23.76	7	23.76	27.72	8	27.72	31.68	9	31.68	35.64	10	35.64	39.60	11	39.60	43.56	12	43.56	47.52	13	47.52	51.48	14	51.48	55.44	15	55.44	59.40	16	59.40	63.36
CKT	A	B																																																						
2	3.96	7.92																																																						
3	7.92	11.88																																																						
4	11.88	15.84																																																						
5	15.84	19.80																																																						
6	19.80	23.76																																																						
7	23.76	27.72																																																						
8	27.72	31.68																																																						
9	31.68	35.64																																																						
10	35.64	39.60																																																						
11	39.60	43.56																																																						
12	43.56	47.52																																																						
13	47.52	51.48																																																						
14	51.48	55.44																																																						
15	55.44	59.40																																																						
16	59.40	63.36																																																						

		2	3	4	5	6	7	8	9																																																
RoHS								<table><tr><td>序号</td><td>品名</td><td>材质</td></tr><tr><td>①</td><td>VH3. 96直针WTB胶芯</td><td>PA66 UL94V-0 米色 白色</td></tr><tr><td>②</td><td>VH3. 96直针WTB端子</td><td>铜合金/表面镀锡</td></tr></table>	序号	品名	材质	①	VH3. 96直针WTB胶芯	PA66 UL94V-0 米色 白色	②	VH3. 96直针WTB端子	铜合金/表面镀锡																																								
序号	品名	材质																																																							
①	VH3. 96直针WTB胶芯	PA66 UL94V-0 米色 白色																																																							
②	VH3. 96直针WTB端子	铜合金/表面镀锡																																																							
								技术指标(Technical Index): 1. 温度范围(Temperature range): -25° C~-85° C. 2. 额定电压(Rated voltage): 250V, AC, DC. 3. 额定电流(Rated current): 7.0A AC, DC. 4. 接触电阻(Contact resistance): ≤20mΩ . 5. 耐压值(Withstanding voltage): 1500V AC/minute. 6. 绝缘电阻(Insulation resistance): ≥1000MΩ.																																																	
								<table><tr><td>CKT</td><td>A</td><td>B</td></tr><tr><td>2</td><td>3. 96</td><td>7. 92</td></tr><tr><td>3</td><td>7. 92</td><td>11. 88</td></tr><tr><td>4</td><td>11. 88</td><td>15. 84</td></tr><tr><td>5</td><td>15. 84</td><td>19. 80</td></tr><tr><td>6</td><td>19. 80</td><td>23. 76</td></tr><tr><td>7</td><td>23. 76</td><td>27. 72</td></tr><tr><td>8</td><td>27. 72</td><td>31. 68</td></tr><tr><td>9</td><td>31. 68</td><td>35. 64</td></tr><tr><td>10</td><td>35. 64</td><td>39. 60</td></tr><tr><td>11</td><td>39. 60</td><td>43. 56</td></tr><tr><td>12</td><td>43. 56</td><td>47. 52</td></tr><tr><td>13</td><td>47. 52</td><td>51. 48</td></tr><tr><td>14</td><td>51. 48</td><td>55. 44</td></tr><tr><td>15</td><td>55. 44</td><td>59. 40</td></tr><tr><td>16</td><td>59. 40</td><td>63. 36</td></tr></table>		CKT	A	B	2	3. 96	7. 92	3	7. 92	11. 88	4	11. 88	15. 84	5	15. 84	19. 80	6	19. 80	23. 76	7	23. 76	27. 72	8	27. 72	31. 68	9	31. 68	35. 64	10	35. 64	39. 60	11	39. 60	43. 56	12	43. 56	47. 52	13	47. 52	51. 48	14	51. 48	55. 44	15	55. 44	59. 40	16	59. 40	63. 36
CKT	A	B																																																							
2	3. 96	7. 92																																																							
3	7. 92	11. 88																																																							
4	11. 88	15. 84																																																							
5	15. 84	19. 80																																																							
6	19. 80	23. 76																																																							
7	23. 76	27. 72																																																							
8	27. 72	31. 68																																																							
9	31. 68	35. 64																																																							
10	35. 64	39. 60																																																							
11	39. 60	43. 56																																																							
12	43. 56	47. 52																																																							
13	47. 52	51. 48																																																							
14	51. 48	55. 44																																																							
15	55. 44	59. 40																																																							
16	59. 40	63. 36																																																							
				<table><tr><td colspan="2">OPERATION</td><td rowspan="2">DRAW</td><td rowspan="2">SCALE</td><td rowspan="2">FIT</td></tr><tr><td>X.X</td><td>±0.30</td></tr></table>		OPERATION		DRAW	SCALE	FIT	X.X	±0.30	深圳市连盛精密连接器有限公司																																												
OPERATION		DRAW	SCALE	FIT																																																					
X.X	±0.30																																																								
		X.XX	±0.20	CHECK	UNIT	mm																																																			
		X.XXX	±0.10																																																						
		Angle	±3°	APPROVE	SHEET	1/1																																																			
REV	DATE	MODIFICATION DESCRIPTION	CHANGE				DIM	TOL	PROJ.	◆≡	PART NO.	1130500038																																													
1		2	3	4	5	6	7	8	9																																																
								TITLE: VH-NA																																																	

	2		3		4		5		6		7		8		9																																																													
RoHS															<table border="1"><tr><td>序号</td><td>品名</td><td>材质</td></tr><tr><td>①</td><td>VH3.96直针WTB胶芯</td><td>PA66 UL94V-0 米色 白色</td></tr><tr><td>②</td><td>VH3.96直针WTB端子</td><td>铜合金/表面镀锡</td></tr></table>		序号	品名	材质	①	VH3.96直针WTB胶芯	PA66 UL94V-0 米色 白色	②	VH3.96直针WTB端子	铜合金/表面镀锡																																																			
序号	品名	材质																																																																										
①	VH3.96直针WTB胶芯	PA66 UL94V-0 米色 白色																																																																										
②	VH3.96直针WTB端子	铜合金/表面镀锡																																																																										
G																G																																																												
F	Top View Dimensions: Pitch: 3.96±0.10 Overall Width: DIMA±0.20 Pin Spacing: 1P, 2P, ... Bottom View Dimensions: Pitch: 3.96±0.05 Overall Width: DIMA±0.10 Pin Diameter: ø1.70±0.05 Label: 适用线路板 (PCB LAYOUT) Isometric View Dimensions: Pitch: 3.96±0.10 Overall Width: DIMA±0.20 Pin Height: 14.0±0.20 Pin Spacing: 1.14±0.05 Side View Dimensions: Pitch: 3.96±0.10 Overall Width: DIMA±0.20 Pin Height: 14.0±0.20 Pin Spacing: 1.14±0.05															F																																																												
E	技术指标(Technical Index): - 温度范围(Temperature range): -25° C~+85° C. - 额定电压(Rated voltage): 250V, AC, DC. - 额定电流(Rated current): 7.0A AC, DC. - 接触电阻(Contact resistance): ≤20mΩ . - 耐压值(Withstanding voltage): 1500V AC/minute. - 绝缘电阻(Insulation resistance): ≥1000MΩ.															E																																																												
D	<table border="1"><thead><tr><th>CKT</th><th>A</th><th>B</th></tr></thead><tbody><tr><td>2</td><td>3.96</td><td>7.92</td></tr><tr><td>3</td><td>7.92</td><td>11.88</td></tr><tr><td>4</td><td>11.88</td><td>15.84</td></tr><tr><td>5</td><td>15.84</td><td>19.80</td></tr><tr><td>6</td><td>19.80</td><td>23.76</td></tr><tr><td>7</td><td>23.76</td><td>27.72</td></tr><tr><td>8</td><td>27.72</td><td>31.68</td></tr><tr><td>9</td><td>31.68</td><td>35.64</td></tr><tr><td>10</td><td>35.64</td><td>39.60</td></tr><tr><td>11</td><td>39.60</td><td>43.56</td></tr><tr><td>12</td><td>43.56</td><td>47.52</td></tr><tr><td>13</td><td>47.52</td><td>51.48</td></tr><tr><td>14</td><td>51.48</td><td>55.44</td></tr><tr><td>15</td><td>55.44</td><td>59.40</td></tr><tr><td>16</td><td>59.40</td><td>63.36</td></tr></tbody></table>															CKT	A	B	2	3.96	7.92	3	7.92	11.88	4	11.88	15.84	5	15.84	19.80	6	19.80	23.76	7	23.76	27.72	8	27.72	31.68	9	31.68	35.64	10	35.64	39.60	11	39.60	43.56	12	43.56	47.52	13	47.52	51.48	14	51.48	55.44	15	55.44	59.40	16	59.40	63.36	D												
CKT	A	B																																																																										
2	3.96	7.92																																																																										
3	7.92	11.88																																																																										
4	11.88	15.84																																																																										
5	15.84	19.80																																																																										
6	19.80	23.76																																																																										
7	23.76	27.72																																																																										
8	27.72	31.68																																																																										
9	31.68	35.64																																																																										
10	35.64	39.60																																																																										
11	39.60	43.56																																																																										
12	43.56	47.52																																																																										
13	47.52	51.48																																																																										
14	51.48	55.44																																																																										
15	55.44	59.40																																																																										
16	59.40	63.36																																																																										
C																C																																																												
B																B																																																												
A	<table border="1"><thead><tr><th>REV</th><th>DATE</th><th>MODIFICATION DESCRIPTION</th><th>CHANGE</th><th>OPERATION</th><th>DRAW</th><th>SCALE</th><th>FIT</th><th colspan="2">深圳市连盛精密连接器有限公司</th></tr></thead><tbody><tr><td></td><td></td><td></td><td></td><td>X.X ±0.30</td><td></td><td>UNIT</td><td>mm</td><td>PART NO.</td><td>1130500038</td></tr><tr><td></td><td></td><td></td><td></td><td>X.XX ±0.20</td><td>CHECK</td><td>SIZE</td><td>A4</td><td>TITLE:</td><td>VH-NA</td></tr><tr><td></td><td></td><td></td><td></td><td>X.XXX ±0.10</td><td></td><td>SHEET</td><td>1/1</td><td></td><td></td></tr><tr><td></td><td></td><td></td><td></td><td>Angle ±3'</td><td>APPROVE</td><td>PROJ.</td><td></td><td></td><td></td></tr><tr><td></td><td></td><td></td><td></td><td>DIM TOL</td><td></td><td></td><td></td><td></td><td></td></tr></tbody></table>															REV	DATE	MODIFICATION DESCRIPTION	CHANGE	OPERATION	DRAW	SCALE	FIT	深圳市连盛精密连接器有限公司						X.X ±0.30		UNIT	mm	PART NO.	1130500038					X.XX ±0.20	CHECK	SIZE	A4	TITLE:	VH-NA					X.XXX ±0.10		SHEET	1/1							Angle ±3'	APPROVE	PROJ.								DIM TOL						A
REV	DATE	MODIFICATION DESCRIPTION	CHANGE	OPERATION	DRAW	SCALE	FIT	深圳市连盛精密连接器有限公司																																																																				
				X.X ±0.30		UNIT	mm	PART NO.	1130500038																																																																			
				X.XX ±0.20	CHECK	SIZE	A4	TITLE:	VH-NA																																																																			
				X.XXX ±0.10		SHEET	1/1																																																																					
				Angle ±3'	APPROVE	PROJ.																																																																						
				DIM TOL																																																																								

- [illegible]

[illegible][illegible]