

		2		3		4		5		6		7		8		9																																																																			
RoHS																																																																																			
G														<table><tr><td>序号</td><td>品名</td><td>材质</td></tr><tr><td>①</td><td>PH2.0弯针WTB胶芯</td><td>PA66 UL94V-0 米色 白色 红色</td></tr><tr><td>②</td><td>PH2.0直针WTB端子</td><td>铜合金/表面镀锡</td></tr></table>				序号	品名	材质	①	PH2.0弯针WTB胶芯	PA66 UL94V-0 米色 白色 红色	②	PH2.0直针WTB端子	铜合金/表面镀锡																																																									
序号	品名	材质																																																																																	
①	PH2.0弯针WTB胶芯	PA66 UL94V-0 米色 白色 红色																																																																																	
②	PH2.0直针WTB端子	铜合金/表面镀锡																																																																																	
F																																																																																			
E																																																																																			
D																																																																																			
C														<table><tr><td>CKT</td><td>A</td><td>B</td><td>CKT</td><td>A</td><td>B</td></tr><tr><td>2</td><td>2.0</td><td>6.0</td><td>12</td><td>22.0</td><td>26.0</td></tr><tr><td>3</td><td>4.0</td><td>8.0</td><td>13</td><td>24.0</td><td>28.0</td></tr><tr><td>4</td><td>6.0</td><td>10.0</td><td>14</td><td>26.0</td><td>30.0</td></tr><tr><td>5</td><td>8.0</td><td>12.0</td><td>15</td><td>28.0</td><td>32.0</td></tr><tr><td>6</td><td>10.0</td><td>14.0</td><td>16</td><td>30.0</td><td>34.0</td></tr><tr><td>7</td><td>12.0</td><td>16.0</td><td>17</td><td>32.0</td><td>36.0</td></tr><tr><td>8</td><td>14.0</td><td>18.0</td><td>18</td><td>34.0</td><td>38.0</td></tr><tr><td>9</td><td>16.0</td><td>20.0</td><td>19</td><td>36.0</td><td>40.0</td></tr><tr><td>10</td><td>18.0</td><td>22.0</td><td>20</td><td>38.0</td><td>42.0</td></tr><tr><td>11</td><td>20.0</td><td>24.0</td><td></td><td></td><td></td></tr></table>				CKT	A	B	CKT	A	B	2	2.0	6.0	12	22.0	26.0	3	4.0	8.0	13	24.0	28.0	4	6.0	10.0	14	26.0	30.0	5	8.0	12.0	15	28.0	32.0	6	10.0	14.0	16	30.0	34.0	7	12.0	16.0	17	32.0	36.0	8	14.0	18.0	18	34.0	38.0	9	16.0	20.0	19	36.0	40.0	10	18.0	22.0	20	38.0	42.0	11	20.0	24.0			
CKT	A	B	CKT	A	B																																																																														
2	2.0	6.0	12	22.0	26.0																																																																														
3	4.0	8.0	13	24.0	28.0																																																																														
4	6.0	10.0	14	26.0	30.0																																																																														
5	8.0	12.0	15	28.0	32.0																																																																														
6	10.0	14.0	16	30.0	34.0																																																																														
7	12.0	16.0	17	32.0	36.0																																																																														
8	14.0	18.0	18	34.0	38.0																																																																														
9	16.0	20.0	19	36.0	40.0																																																																														
10	18.0	22.0	20	38.0	42.0																																																																														
11	20.0	24.0																																																																																	
B		技术指标(Technical Index): 1. 工作温度(Temperature range): -25° C~85° C. 2. 额定电压(Rated voltage): 250V DC/AC(rms). 3. 额定电流(Rated current): 2.0A AC, DC. 4. 接触电阻(Contact resistance): ≤25mΩ. 5. 耐压值(Withstanding voltage): 500V AC/minute. 6. 绝缘电阻(Insulation resistance): ≥1000MΩ. 7. 产品料号(Product material No.):				TYPE 1(无K脚)				TYPE 2(打K脚)				SECTION A-A																																																																					
A		<table><tr><td>REV</td><td>DATE</td><td>MODIFICATION DESCRIPTION</td><td>CHANGE</td></tr><tr><td>1</td><td>2</td><td>3</td><td>4</td></tr></table>				REV	DATE	MODIFICATION DESCRIPTION	CHANGE	1	2	3	4	<table><tr><td colspan="2">OPERATION</td><td rowspan="2">DRAW</td><td rowspan="2">SCALE</td><td rowspan="2">FIT</td><td colspan="2" rowspan="4">深圳市连盛精密连接器有限公司</td></tr><tr><td>X.X</td><td>±0.30</td></tr><tr><td>X.XX</td><td>±0.20</td><td rowspan="2">CHECK</td><td rowspan="2">SIZE</td><td rowspan="2">A4</td></tr><tr><td>X.XXX</td><td>±0.10</td></tr><tr><td>Angle</td><td>±3°</td><td rowspan="2">APPROVE</td><td rowspan="2">SHEET</td><td rowspan="2">1/1</td></tr><tr><td>DIM</td><td>TOL</td><td>PROJ.</td><td>◆</td><td>TITLE:</td><td>PH-NA</td></tr></table>				OPERATION		DRAW	SCALE	FIT	深圳市连盛精密连接器有限公司		X.X	±0.30	X.XX	±0.20	CHECK	SIZE	A4	X.XXX	±0.10	Angle	±3°	APPROVE	SHEET	1/1	DIM	TOL	PROJ.	◆	TITLE:	PH-NA	<table><tr><td colspan="2">PART NO.</td><td>1130300171</td></tr><tr><td colspan="2">TITLE:</td><td>PH-NA</td></tr></table>				PART NO.		1130300171	TITLE:		PH-NA																													
REV	DATE	MODIFICATION DESCRIPTION	CHANGE																																																																																
1	2	3	4																																																																																
OPERATION		DRAW	SCALE	FIT	深圳市连盛精密连接器有限公司																																																																														
X.X	±0.30																																																																																		
X.XX	±0.20	CHECK	SIZE	A4																																																																															
X.XXX	±0.10																																																																																		
Angle	±3°	APPROVE	SHEET	1/1																																																																															
DIM	TOL				PROJ.	◆	TITLE:	PH-NA																																																																											
PART NO.		1130300171																																																																																	
TITLE:		PH-NA																																																																																	