


RoHS



REV.	DESCRIPTION.	ECN NO.	DWG.	CKD.	APPD.	DATE.
A	NEW		严亮	杜江	李永峰	2021-1-15

规格说明: Specifications:

电气特性: Electrical:

1. 额定电流: Current Rating
1.5A/contact terminal
2. 额定电压: Voltage Rating
30V DC
3. 接触阻抗: Contact Resistance
30 milliohms MAX
4. 耐电压: Dielectric Withstanding Voltage:
500 V AC AT Sea Level
5. 绝缘阻抗: Insulation Resistance:
1000 MEGA ohms MIN

物理性能: Mechanical:

1. 插拔力: Connector Mate and Unmate Force
Mate force: 3.57kgf (MAX)
Unmate force: 1.02kgf (MIN)
2. 端子保持力: Terminal Retention
1.0kgf (MIN)

原材料: Material:


1. 塑胶: Housing:
Hing Temperature Thermoplastics,
2. 端子: Contact: Copper Alloy C2680
3. 外壳: Shell: Copper Alloy C2680/SPCC

电镀: Finish:

1. 端子: Contact: Plated Gold in Mating Area;
Tin On Solder Tails
端子四周镀30U" (MIN) 镍, 焊接区域镀锡80-120U", 接触点镀金
2. 外壳: Shell:
外壳四周镀50U" (MIN) 镍
Nickel Plating

TOLERANCES UNLESS OTHERWISE SPECIFIED		东莞市辉焕精密有限公司	
UNIT (MM)	ORIGINAL DATA	TITLE	
X. ±0.55	2021-1-15	USB A/F 10.0侧插短体PBT黑胶直边	
X.X ±0.35			
X.XX ±0.25			
X.XXX ±0.15			
ANGLE ±2°			
3RD. ANGLE'S	CKD.	PART NO.	SCALE
	杜江	USB-DIP-002	1:1
	APPD.	DWG NO.	SIZE
	李永峰	USB-DIP-002	A4
		SHEET	REV.
		1/2	A

REV.	DESCRIPTION.	ECN NO.	DWG.	CKD.	APPD.	DATE.
A	NEW	钟林	陈晓军	黄河勇	2022-04-15	



TOLERANCES UNLESS OTHERWISE SPECIFIED		东莞市辉煌精密有限公司		
UNIT	(MM)	ORIGINAL DATA	TITLE	
X.	±0.55	2022-04-15	USB AF 侧插短体10.0 包装图	
X.X	±0.35	DWG.	钟林	
X.XX	±0.25	CKD.	陈晓军	PART NO.
X.XXX	±0.15	APPD.	黄河勇	USB-DIP-002
ANGEL	±2°			SCALE 1:1
3RD,ANGLE'S				SIZE A4
				SHEET 2/2
				REV. A