




TE Internal #: 2205094-1

Wire-to-Board, 3 Position, 2 mm [.078 in] Centerline, 63.5 mm [2.5 in] Length, Printed Circuit Board, Power & Signal, Wire-to-Board Jumpers & Shunts

[View on TE.com >](#)

Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Jumpers & Shunts



Connector System: **Wire-to-Board**

Number of Positions: **3**

Centerline (Pitch): **2 mm [.078 in]**

Product Length: **63.5 mm [2.5 in]**

Connector & Contact Terminates To: **Printed Circuit Board**

Features

Product Type Features

Compatible With Discrete Wire Type	Solid
Connector System	Wire-to-Board
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Conductors	3
Number of Rows	1
Number of Positions	3

Electrical Characteristics

Operating Voltage	200 VAC
Impedance	116 Ω

Body Features

Jumper Insulation Material	Aramid Paper
----------------------------	--------------

Contact Features

Pin Arrangement (Right)	A
-------------------------	---



Pin Arrangement (Left)	A
Contact Current Rating (Max)	2 A

Housing Features

Centerline (Pitch)	2 mm[.078 in]
--------------------	---------------

Dimensions

Wire Size	26 AWG
Product Length	63.5 mm[2.5 in]

Usage Conditions

Operating Temperature Range	-40 – 125 °C[-40 – 257 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts



TE Part # 2205333-1
FSN-72Z-5



TE Part # 2205127-1
FSN-7.8A-8



TE Part # 1-6437152-5
FSN-71.5A-14

Customers Also Bought



TE Part # TRA9023P
OMNI,SB,Ph,902-928MHZ 3,PMT




TE Part # CSI-RGFE-100-UFFR
RP-SMA to U.FL/MHF1 100mm 1.13 OD



TE Part # CAT-104MTA-NTPNR
MTA Receptacle: Nylon, Tin Plated, 2.54 mm



TE Part # 2-640445-4
24P MTA156 HDR ASSY FL/STR SN



TE Part # 1-640550-3
13P MTA100 COVER



TE Part # 1676309-2
RN 0805 348R 0.1% 10PPM 1KRL



TE Part # 2176612-5
EP 3W (SS) 1R5 5%



TE Part # 1-2176612-3
EP 3W (SS) 3R3 5%



TE Part # LBT3400-L
MOUNT,TKG,3/4 SS,STD,L BRKT

Documents

Product Drawings
FSN-72.5A-3

English

Product Specifications
Product Specification

English



[Agency Approvals](#)

[UL Report](#)

English