




- 1.High common mode impedance at high frequency cause excellent noise suppression performance.
- 2.CWCM2012F series realizes small size and low profile. 2.0x1.2x1.2 mm.
- 3.100% Lead(Pb) & Halogen-Free and RoHS compliant.
- 4.Operating temperature-40~+125 C
- 5.FOR LAN Module application


Part Number	Common mode Impedance (Ω)	Test Frequency (MHz)	DC Resistance (Ω) max.	Rated Current (mA)max.	Rated Volt. (Vdc)max.	Withstand Volt. (Vdc) max.	IR (Ω) min.
CWCM2012F-2-300T04	30±25%	100	0.25	400	50	125	10M
CWCM2012F-2-670T04	67±25%	100	0.25	400	50	125	10M
CWCM2012F-2-750T04	75±25%	100	0.30	400	50	125	10M
CWCM2012F-2-900T04	90±25%	100	0.30	400	50	125	10M
CWCM2012F-2-121T04	120±25%	100	0.30	400	50	125	10M
CWCM2012F-2-161T03	160±25%	100	0.35	350	50	125	10M
CWCM2012F-2-181T03	180±25%	100	0.35	350	50	125	10M
CWCM2012F-2-201T03	200±25%	100	0.40	300	50	125	10M
CWCM2012F-2-221T03	220±25%	100	0.40	300	50	125	10M
CWCM2012F-2-261T03	260±25%	100	0.40	300	50	125	10M
CWCM2012F-2-361T03	360±25%	100	0.50	300	50	125	10M
CWCM2012F-2-381T03	380±25%	100	0.50	400	50	125	10M
CWCM2012F-2-801	800±25%	100	0.30	400	50	125	10M
CWCM2012F-2-102S	1000±25%	100	0.30	400	50	125	10M

MECHANICAL



Dimension: mm

SCHEMATICS



SOLDERING IRON




Fig.1






Fig.2

IMPEDEANCE FREQUENCY




TAPING AND PACKING



Quantity (pcs):
2000 PCS PER REEL
5 REELS PER CARTON
10000PCS PER CARTON

Reel



Dimensions in mm