

文件
分发
业务
资材
生产
注塑
冲压
工程
IQC
IPQC
文控

重点尺寸

CPK管控


CPK序号

尺寸

修改版次

XX

RoHS



REV.	DESCRIPTION.	ECN NO.	DWG.	CKD.	APPD.	DATE.
A	NEW		严亮	杜江	李永锋	2021-1-15

- 规格说明:Specifications:
- 电气特性:Electrical:
- 额定电流: Current Rating
1.5A/contact terminal
 - 额定电压: Voltage Rating
30V DC
 - 接触阻抗:Contact Resistance
30 milliohms MAX
 - 耐电压:Dielectnic Withstanding Voitage:
500 V AC AT Sea Levol
 - 绝缘阻抗:Lnsulation Resistance:
1000MEGA ohms MIN


- 物理性能:Mechanical:
- 插拔力: Cnnector Mate and Unmate Force
Mate force:35N (MAX)
Unmate force:10N (MIN)
 - 端子保持力: Terminal Retenion
10N (MIN)

- 原材料:Material:
- 塑胶:Housing:
Hing Temperature Thermaplastics,
U1 94V-0 PBT Black/White
 - 端子:Contact:Copper Alloy C2680/C5191
 - 外壳:Shell: Copper Alloy C2680/SPCC

- 电镀:Finish:
- 端子:Contact: Piated Gold in Mating Area;
Tin On Solder Talls
 - 外壳:Shell:
Nickel Plating


TOLERANCES UNLESS OTHERWISE SPECIFIED					
UNIT (MM)	X.	±0.55	ORIGINAL DATA 2021-1-15		
	X.X	±0.35			
	X.XX	±0.25	DWG. 严亮		
	X.XXX	±0.15			
ANGEL		±2°	CKD. 杜江		
3RD.ANGLE'S					
			APPD. 李永锋		
			TITLE USB AF 90度双层弯脚有后盖 PBT 白胶卷边		
			PART NO. USB-DIP-088	SCALE 1:1	SIZE A4
			DWG NO. USB-DIP-088	SHEET 1/2	REV. A

RoHS




- ① PE真空盒(1Set).
- ② 100Pcs/盒, 每5盒为一捆.

REV.	DESCRIPTION.	ECN NO.	DWG.	CKD.	APPD.	DATE.
A	NEW		严亮	杜江	李永锋	2021-1-15



- ③ 20盒/箱(2k).



- ④ 每箱平放10盒*2, 若尾数箱在空间处加装填充物.
- ⑤ 外箱用透明胶纸带封箱
- ⑥ 依图示粘贴产品或ROHS标签.

备注:

1. PE真空盒:L225*W200*H20mm/set
2. 每盒装成品100Pcs, 每5盒叠放一起, 用PE膜缠绕;
3. 每箱装20盒(2K);
4. 外箱尺寸与规格: 40.5*23*22.5CM
5. 外箱用透明胶纸带封"工"字型;

TOLERANCES UNLESS OTHERWISE SPECIFIED		东莞市辉焕精密有限公司			
UNIT	(MM)	ORIGINAL DATA 2021-1-15	TITLE USB AF 90度双层弯脚有后盖PBT 白胶卷边		
X. ±0.55 X.X ±0.35 X.XX ±0.25 X.XXX ±0.15 ANGEL ±2°		DWG. 严亮			
3RD.ANGLE'S 		CKD. 杜江	PART NO. USB-DIP-088	SCALE 1:1	SIZE A4
		APPD. 李永锋	DWG NO. USB-DIP-088	SHEET 2/2	REV. A