







REV.	DESCRIPTION.	ECN NO.	DWG.	CKD.	APPD.	DATE.
A	NEW		钟 林	陈晓军	黄河勇	2022-4-15

规格说明: Specifications:

电气特性:Electrical:

1. 额定电流: Current Rating
1.5A/contact terminal
2. 额定电压: Voltage Rating
30V DC
3. 接触阻抗: Contact Resistance
30 milliohms MAX
4. 耐电压: Dielectric Withstanding Voltage:
500 V AC AT Sea Level
5. 绝缘阻抗: Insulation Resistance:
1000MEGA ohms MIN

物理性能:Mechanical:


1. 插拔力: Connector Mate and Unmate Force
Mate force: 3.57kgf (MAX)
Unmate force: 1.02kgf (MIN)
2. 端子保持力: Terminal Retention
1.2kgf (MIN)

原材料:Material:

1. 塑胶:Housing:
Hing Temperature Tnermaplastics,
UL 94V-0 LCP Beige/Black
2. 端子>Contact:Copper Alloy C2680
3. 外壳:Shell: Copper Alloy C2680/SPCC

电镀:Finish:

1. 端子:Contact: Plated Gold in Mating Area;
Tin On Solder Talls
2. 外壳:Shell:
Nickel Plating

TOLERANCES UNLESS OTHERWISE SPECIFIED		东莞市辉焕精密有限公司			
UNIT (MM)		ORIGINAL DATA		TITLE	
X.	±0.55	2022-4-15		USB A/F 直角1.75卷边1.0柱黑胶	
X.X	±0.35	DWG.			
X.XX	±0.25	钟林			
X.XXX	±0.15	CKD.		PART NO.	SCALE
ANGEL	±2°	陈晓军		USB-SMT-002	1:1
3RD.ANGLE'S		APPD.		DWG NO.	SHEET
		黄河勇		USB-SMT-002	1/2
					REV.
					A

