



**Part Number :** [1202530528](#)

**Product Description :** Contrinex Inductive Sensor, M5 Housing, 1.5mm Operating Distance, Embeddable, PNP, NC, 3-pin M8 Connector, 38mm Housing Length

**Series Number :** 120253

**Status :** Not Recommended For New Design

**Product Category :** Inductive and Photoelectric Sensors

**Engineering Number :** DW-AS-624-M5



## Documents & Resources

### Specifications

[1202530521-000.pdf](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	ⓘ per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

## UKCA - Declaration of Conformity

## CE - Declaration of Conformity

## **Part Details**

### **General**

Status	Not Recommended For New Design
Category	Inductive Sensors
Series	120253
Description	Contrinex Inductive Sensor, M5 Housing, 1.5mm Operating Distance, Embeddable, PNP, NC, 3-pin M8 Connector, 38mm Housing Length
IP Rating	IP67
Product Name	Contrinex
Type	Inductive
UPC	191130069231

### **Electrical**

Output	NC
Polarity	PNP
Switching Frequency	≤ 3000 Hz

### **Physical**

Connection	Connector (M8, 3-pin)
Length	38mm
Material - Housing	Stainless Steel
Material - Sensing Face	POM
Mounting Style	Embeddable
Operating Distance	1.5mm
Output	NC
Sensor Housing Size	M5

Temperature Range - Operating

-25° to +70°C

---

This document was generated on Oct 30, 2025