

## 1. General Description

---

The 74AHC1G125 and 74AHCT1G125 are single buffer/line drivers with 3-state outputs. Inputs are overvoltage tolerant. This feature allows the use of these devices as translators in mixed voltage environments.

## 2. Features and Benefits

---


- Wide supply voltage range from 2.0 V to 5.5 V
- Overvoltage tolerant inputs to 5.5 V
- High noise immunity
- CMOS low power dissipation
- Latch-up performance exceeds 200 mA
- Symmetrical output impedance
- Balanced propagation delays
- Input levels:
  - For 74AHC1G125: CMOS level
  - For 74AHCT1G125: TTL level
- ESD protection:
  - HBM ANSI/ESDA/JEDEC JS-001 Class 3A exceeds 7000 V
  - CDM ANSI/ESDA/JEDEC JS-002 Class C3 exceeds 2000 V
- Multiple package options

### 3. Ordering Information

**Table 1. Ordering information**


Type number	Package		
	Name	Description	Quantity
74AHC1G125GV	SOT23-5L	SOT23 package, 5 pins 2.92 mm × 1.6 mm; 1.25 mm (Max) height	3000
74AHCT1G125GV			
74AHC1G125GW	SOT353	SOT353 package, 5 pins 2.1 mm × 1.25 mm; 1.1 mm (Max) height	3000
74AHCT1G125GW			
74AHC1G125DRL	SOT553	SOT553 package, 5 pins 1.6 mm × 1.2 mm; 0.6 mm (Max) height	3000
74AHCT1G125DRL			

### 4. Function Diagram



## 5. Pinning Information

### 5.1. Pinning



### 5.2. Pin description

Table 2. Pin description

Symbol	Pin	Description
$\overline{OE}$	1	Output enable input
A	2	Data input
GND	3	Ground (0V)
Y	4	Data output
V <sub>CC</sub>	5	Supply voltage

## 6. Functional Description

Table 3. Function table

H = HIGH voltage level; L = LOW voltage level; X = don't care; Z = high-impedance OFF-state

Input		Output
$\overline{OE}$	A	Y
L	L	L
L	H	H
H	X	Z

## 7. Absolute Maximum Ratings

Stresses exceeding the absolute maximum ratings may damage the device. The device may not function or be operable above the recommended operating conditions and stressing the parts to these levels is not recommended. In addition, extended exposure to stresses above the recommended operating conditions may affect device reliability. The absolute maximum ratings are stress ratings only.

**Table 4. Absolute Maximum Ratings**

In accordance with the Absolute Maximum Rating System (IEC 60134). Voltages are referenced to GND.

Symbol	Parameter	Conditions	Min	Max	Unit
$V_{CC}$	supply voltage		-0.5	7.0	V
$V_I$	input voltage		-0.5	7.0	V
$I_{IK}$	input clamping current	$V_I < -0.5\text{ V}$	-20		mA
$I_{OK}$	output clamping current	$V_O < -0.5\text{ V}$ or $V_O > V_{CC} + 0.5\text{ V}$ [1]		$\pm 20$	mA
$I_O$	output current	$-0.5\text{ V} < V_O < V_{CC} + 0.5\text{ V}$		$\pm 25$	mA
$I_{CC}$	supply current			75	mA
$I_{GND}$	ground current		-75		mA
$P_{tot}$	total power dissipation	$T_{amb} = -40\text{ °C}$ to $+125\text{ °C}$		250	mW
$T_{stg}$	storage temperature		-65	150	°C

[1] The input and output voltage ratings may be exceeded if the input and output current ratings are observed.

## 8. Recommended Operating Conditions

The Recommended Operating Conditions table defines the conditions for actual device operation. Recommended operating conditions are specified to ensure optimal performance to the datasheet specifications. MDD does not recommend exceeding them or designing to Absolute Maximum Ratings.

**Table 5. Recommended Operating Conditions**

Symbol	Parameter	Conditions	74AHC1G125			74AHCT1G125			Unit
			Min	Typ	Max	Min	Typ	Max	
$V_{CC}$	supply voltage		2.0	5.0	5.5	2.0	5.0	5.5	V
$V_I$	input voltage		0		5.5	0		5.5	V
$V_O$	output voltage		0		$V_{CC}$	0		$V_{CC}$	V
$T_{amb}$	ambient temperature		-40	25	125	-40	25	125	°C
$\Delta t/\Delta V$	input transition rise and fall rate	$V_{CC} = 3.3\text{ V} \pm 0.3\text{ V}$			100			100	ns/V
		$V_{CC} = 5.0\text{ V} \pm 0.5\text{ V}$			20			20	ns/V

## 9. Static Characteristics

**Table 6. Static characteristics**

At recommended operating conditions. Voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions	-40 °C to +85 °C			-40 °C to +125 °C		Unit
			Min	Typ[1]	Max	Min	Max	
<b>74AHC1G125</b>								
V <sub>IH</sub>	HIGH-level input voltage	V <sub>CC</sub> = 2.0 V	1.5			1.5		V
		V <sub>CC</sub> = 3.0 V	2.1			2.1		V
		V <sub>CC</sub> = 5.5 V	3.85			3.85		V
V <sub>IL</sub>	LOW-level input voltage	V <sub>CC</sub> = 2.0 V			0.5		0.5	V
		V <sub>CC</sub> = 3.0 V			0.9		0.9	V
		V <sub>CC</sub> = 5.5 V			1.65		1.65	V
V <sub>OH</sub>	HIGH-level output voltage	V <sub>I</sub> = V <sub>IH</sub> or V <sub>IL</sub>						
		I <sub>O</sub> = -50 μA; V <sub>CC</sub> = 2.0 V	1.9	2.0		1.9		V
		I <sub>O</sub> = -50 μA; V <sub>CC</sub> = 3.0 V	2.9	3.0		2.9		V
		I <sub>O</sub> = -50 μA; V <sub>CC</sub> = 4.5 V	4.4	4.5		4.4		V
		I <sub>O</sub> = -4.0 mA; V <sub>CC</sub> = 3.0 V	2.48	2.93		2.40		V
		I <sub>O</sub> = -8.0 mA; V <sub>CC</sub> = 4.5 V	3.80	4.39		3.70		V
V <sub>OL</sub>	LOW-level output voltage	V <sub>I</sub> = V <sub>IH</sub> or V <sub>IL</sub>						
		I <sub>O</sub> = 50 μA; V <sub>CC</sub> = 2.0 V		0	0.1		0.1	V
		I <sub>O</sub> = 50 μA; V <sub>CC</sub> = 3.0 V		0	0.1		0.1	V
		I <sub>O</sub> = 50 μA; V <sub>CC</sub> = 4.5 V		0	0.1		0.1	V
		I <sub>O</sub> = 4.0 mA; V <sub>CC</sub> = 3.0 V		0.05	0.44		0.55	V
		I <sub>O</sub> = 8.0 mA; V <sub>CC</sub> = 4.5 V		0.07	0.44		0.55	V
I <sub>OZ</sub>	OFF-state output current	V <sub>CC</sub> = 5.5 V; V <sub>I</sub> = V <sub>CC</sub> or GND		0.01	2.5		10	μA
I <sub>I</sub>	input leakage current	V <sub>I</sub> = 5.5 V or GND ; V <sub>CC</sub> = 0 V to 5.5 V		±0.01	±1.0		±2.0	μA
I <sub>CC</sub>	supply current	V <sub>I</sub> = V <sub>CC</sub> or GND ; I <sub>O</sub> = 0 A ; V <sub>CC</sub> = 5.5 V		0.01	10		40	μA
C <sub>I</sub>	input capacitance			3.5				pF

**74AHC1G125; 74AHCT1G125**
**Bus buffer/line driver; 3-state**

Symbol	Parameter	Conditions	-40 °C to +85 °C			-40 °C to +125 °C		Unit
			Min	Typ[1]	Max	Min	Max	
<b>74AHCT1G125</b>								
V <sub>IH</sub>	HIGH-level input voltage	V <sub>CC</sub> = 2.0 V	1.0			1.0		V
		V <sub>CC</sub> = 3.3 V	1.5			1.5		V
		V <sub>CC</sub> = 4.5 V to 5.5 V	2.0			2.0		V
V <sub>IL</sub>	LOW-level input voltage	V <sub>CC</sub> = 2.0 V			0.3		0.3	V
		V <sub>CC</sub> = 3.3 V			0.55		0.55	V
		V <sub>CC</sub> = 4.5 V to 5.5 V			0.8		0.8	V
V <sub>OH</sub>	HIGH-level output voltage	V <sub>I</sub> = V <sub>IH</sub> or V <sub>IL</sub> ;						
		I <sub>O</sub> = -50 μA; V <sub>CC</sub> = 2.0 V	1.9	2.0		1.9		V
		I <sub>O</sub> = -50 μA; V <sub>CC</sub> = 3.0 V	2.9	3.0		2.9		V
		I <sub>O</sub> = -50 μA; V <sub>CC</sub> = 4.5 V	4.4	4.5		4.4		V
		I <sub>O</sub> = -4.0 mA; V <sub>CC</sub> = 3.0 V	2.48	2.93		2.4		V
		I <sub>O</sub> = -8.0 mA; V <sub>CC</sub> = 4.5 V	3.80	4.39		3.70		V
V <sub>OL</sub>	LOW-level output voltage	V <sub>I</sub> = V <sub>IH</sub> or V <sub>IL</sub> ;						
		I <sub>O</sub> = 50 μA; V <sub>CC</sub> = 2.0 V		0	0.1		0.1	V
		I <sub>O</sub> = 50 μA; V <sub>CC</sub> = 3.0 V		0	0.1		0.1	V
		I <sub>O</sub> = 50 μA; V <sub>CC</sub> = 4.5 V		0	0.1		0.1	V
		I <sub>O</sub> = 4.0 mA; V <sub>CC</sub> = 3.0 V		0.05	0.44		0.55	V
		I <sub>O</sub> = 8.0 mA; V <sub>CC</sub> = 4.5 V		0.07	0.44		0.55	V
I <sub>OZ</sub>	OFF-state output current	V <sub>CC</sub> = 5.5 V; V <sub>I</sub> = V <sub>CC</sub> or GND		0.01	2.5		10	μA
I <sub>I</sub>	input leakage current	V <sub>I</sub> = 5.5 V or GND ; V <sub>CC</sub> = 0 V to 5.5 V		±0.01	±1.0		±2.0	μA
I <sub>CC</sub>	supply current	V <sub>I</sub> = V <sub>CC</sub> or GND ; I <sub>O</sub> = 0 A ; V <sub>CC</sub> = 5.5 V		0.01	10		40	μA
ΔI <sub>CC</sub>	additional supply current	per input pin ; V <sub>I</sub> = 3.4 V ; other inputs at V <sub>CC</sub> or GND ; I <sub>O</sub> = 0 A; V <sub>CC</sub> = 5.5 V		0.23	1.35		1.35	mA
C <sub>I</sub>	input capacitance			3.5				pF

[1]All typical values are measured at T<sub>amb</sub> = 25°C.

## 10. Dynamic Characteristics

**Table 7. Dynamic characteristics**

Voltages are referenced to GND (ground = 0 V); for test circuit see Fig. 7.

Symbol	Parameter	Conditions	-40 °C to +85 °C			-40 °C to +125 °C		Unit
			Min	Typ[1]	Max	Min	Max	
<b>74AHC1G125</b>								
$t_{pd}$	propagation delay	A to Y; see Fig. 5 [2]						
		$V_{CC} = 3.0\text{ V to }3.6\text{ V}, C_L = 15\text{ pF}$	1.0	5.7	8.5	1.0	9.0	ns
		$V_{CC} = 4.5\text{ V to }5.5\text{ V}, C_L = 15\text{ pF}$	1.0	3.9	5.5	1.0	6.0	ns
$t_{en}$	enable time	$\overline{OE}$ to Y; see Fig. 6 [2]						
		$V_{CC} = 3.0\text{ V to }3.6\text{ V}, C_L = 15\text{ pF}$	1.0	6.3	10.0	1.0	11.0	ns
		$V_{CC} = 4.5\text{ V to }5.5\text{ V}, C_L = 15\text{ pF}$	1.0	4.5	6.5	1.0	7.0	ns
$t_{dis}$	disable time	$\overline{OE}$ to Y; see Fig. 6 [2]						
		$V_{CC} = 3.0\text{ V to }3.6\text{ V}, C_L = 15\text{ pF}$	1.0	4.7	14.0	1.0	14.5	ns
		$V_{CC} = 4.5\text{ V to }5.5\text{ V}, C_L = 15\text{ pF}$	1.0	3.9	7.5	1.0	8.0	ns
$C_{PD}$	power dissipation capacitance	$C_L = 15\text{ pF}; f = 1\text{ MHz}; V_I = \text{GND to }V_{CC};$ [3]		20				pF
<b>74AHCT1G125</b>								
$t_{pd}$	propagation delay	A to Y; see Fig. 5 [2]						
		$V_{CC} = 2.0\text{ V}, C_L = 15\text{ pF}$		44				ns
		$V_{CC} = 3.3\text{ V}, C_L = 15\text{ pF}$	2.0	5.5	12.5	2.0	13.0	ns
		$V_{CC} = 4.5\text{ V to }5.5\text{ V}, C_L = 15\text{ pF}$	1.0	5.0	7.5	1.0	8.0	ns
$t_{en}$	enable time	$\overline{OE}$ to Y; see Fig. 6 [2]						
		$V_{CC} = 2.0\text{ V}, C_L = 15\text{ pF}$		79				ns
		$V_{CC} = 3.3\text{ V}, C_L = 15\text{ pF}$	7.0	12.9	17.0	7.0	17.5	ns
		$V_{CC} = 4.5\text{ V to }5.5\text{ V}, C_L = 15\text{ pF}$	4.0	8.1	11	4.0	11.5	ns
$t_{dis}$	disable time	$\overline{OE}$ to Y; see Fig. 6 [2]						
		$V_{CC} = 2.0\text{ V}, C_L = 15\text{ pF}$		12				ns
		$V_{CC} = 3.3\text{ V}, C_L = 15\text{ pF}$	3.0	6.4	9.5	3.0	10.0	ns

## 74AHC1G125; 74AHCT1G125

Bus buffer/line driver; 3-state

		$V_{CC} = 4.5\text{ V to } 5.5\text{ V}, C_L = 15\text{ pF}$	2.0	4.1	6.5	2.0	7.0	ns
$C_{PD}$	power dissipation capacitance	$C_L = 15\text{ pF}; f = 1\text{ MHz}; V_I = \text{GND to } V_{CC};$ [3]		21				pF

[1] Typical values are measured at  $T_{amb} = 25\text{ }^\circ\text{C}$  and  $V_{CC} = 2.0\text{ V}, 3.3\text{ V}$  and  $5.0\text{ V}$  respectively.

[2]  $t_{pd}$  is the same as  $t_{PLH}$  and  $t_{PHL}$ .

$t_{en}$  is the same as  $t_{PZL}$  and  $t_{PZH}$ .

$t_{dis}$  is the same as  $t_{PLZ}$  and  $t_{PHZ}$ .

[3]  $C_{PD}$  is used to determine the dynamic power dissipation ( $P_D$  in  $\mu\text{W}$ ).

$P_D = C_{PD} \times V_{CC}^2 \times f_i \times N + \Sigma(C_L \times V_{CC}^2 \times f_o)$  where:

$f_i$  = input frequency in MHz;

$f_o$  = output frequency in MHz;


$C_L$  = output load capacitance in pF;

$V_{CC}$  = supply voltage in V;

$N$  = number of inputs switching;

$\Sigma(C_L \times V_{CC}^2 \times f_o)$  = sum of outputs.


### 10.1. Waveforms and test circuit






# 74AHC1G125; 74AHCT1G125

## Bus buffer/line driver; 3-state




**Table 8. Measurement points**

Type	Supply Voltage	Input		Output		
	$V_{CC}$	$V_I$	$V_M$	$V_M$	$V_X$	$V_Y$
74AHC1G125	3.0 V - 5.5 V	GND to $V_{CC}$	$0.5 \times V_{CC}$	$0.5 \times V_{CC}$	$V_{OL} + 0.3 \text{ V}$	$V_{OH} - 0.3 \text{ V}$
74AHCT1G125	2.0 V	GND to $V_{CC}$	$0.5 \times V_{CC}$	$0.5 \times V_{CC}$	$V_{OL} + 0.15 \text{ V}$	$V_{OH} - 0.15 \text{ V}$
	3.3 V	GND to 3.0 V	1.5 V	$0.5 \times V_{CC}$	$V_{OL} + 0.3 \text{ V}$	$V_{OH} - 0.3 \text{ V}$
	4.5 V - 5.5 V	GND to 3.0 V	1.5 V	$0.5 \times V_{CC}$	$V_{OL} + 0.3 \text{ V}$	$V_{OH} - 0.3 \text{ V}$



## 74AHC1G125; 74AHCT1G125

Bus buffer/line driver; 3-state



**Table 9. Test data**


Type	Input	Load		$V_{EXT}$		
	$t_r = t_f$	$C_L$	$R_L$	$t_{PLH}, t_{PHL}$	$t_{PZH}, t_{PHZ}$	$t_{PZL}, t_{PLZ}$
74AHC1G125	$\leq 2.5$ ns	15 pF	500 $\Omega$	open	GND	$V_{CC}$
74AHCT1G125	$\leq 2.5$ ns	15 pF	500 $\Omega$	open	GND	$V_{CC}$

## 11. Package Outline

SOT23-5L

74AHC1G125; 74AHCT1G125

Bus buffer/line driver; 3-state




Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	1.050	1.250	0.041	0.049
A1	0.000	0.100	0.000	0.004
A2	1.050	1.150	0.041	0.045
b	0.300	0.500	0.012	0.020
c	0.100	0.200	0.004	0.008
D	2.820	3.020	0.111	0.119
E1	1.500	1.700	0.059	0.067
E	2.650	2.950	0.104	0.116
e	0.950(BSC)		0.037(BSC)	
e1	1.800	2.000	0.071	0.079
L	0.300	0.600	0.012	0.024
L1	0.600REF.		0.024REF.	
theta	0°	8°	0°	8°

SOT353

74AHC1G125; 74AHCT1G125


Bus buffer/line driver; 3-state



SOT553

74AHC1G125; 74AHCT1G125

Bus buffer/line driver; 3-state



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	0.525	0.600	0.021	0.024
A1	0.000	0.050	0.000	0.002
e	0.450	0.550	0.018	0.022
c	0.090	0.160	0.004	0.006
D	1.500	1.700	0.059	0.067
b	0.170	0.270	0.007	0.011
E1	1.100	1.300	0.043	0.051
E	1.500	1.700	0.059	0.067
L	0.100	0.300	0.004	0.012
$\theta$	7 ° REF.		7 ° REF.	

## 12. Abbreviations

**Table 10. Abbreviations**

Acronym	Description
CMOS	Complementary Metal-Oxide Semiconductor
DUT	Device Under Test
ESD	ElectroStatic Discharge
HBM	Human Body Model
CDM	Charged Device Model
TTL	Transistor-Transistor Logic

## 13. Revision History

**Table 11. Revision history**

Document ID	Release Date	Data sheet status	Change notice	Supersedes
74AHC_AHCT1G125 Rev. 1.0	Apr 20, 2024	Product datasheet		