







RoHS

| 序号 | 品名           | 材质                    |
|----|--------------|-----------------------|
| ①  | HY2.0直针WTB胶芯 | PA66 UL94V-0 米色<br>白色 |
| ②  | HY2.0直针WTB端子 | 铜合金/表面镀锡              |




SECTION A-A

技术指标(Technical Index):

- 温度范围(Temperature range): -25° C~+85° C.
- 额定电压(Rated voltage): 200V, AC.
- 额定电流(Rated current): 2.0A AC,DC.
- 接触电阻(Contact resistance): ≤25m Ω .
- 耐压值(Withstanding voltage): 500V AC/minute.
- 绝缘电阻(Insulation resistance): ≥1000M Ω.
- 产品料号(Product material No.):

TYPE 1(无K脚)

TYPE 2(打K脚)



适用线路板(PCB LAYOUT)

| CKT | A    | B    | CKT | A    | B    |
|-----|------|------|-----|------|------|
| 2   | 2.0  | 6.0  | 12  | 22.0 | 26.0 |
| 3   | 4.0  | 8.0  | 13  | 24.0 | 28.0 |
| 4   | 6.0  | 10.0 | 14  | 26.0 | 30.0 |
| 5   | 8.0  | 12.0 | 15  | 28.0 | 32.0 |
| 6   | 10.0 | 14.0 | 16  | 30.0 | 34.0 |
| 7   | 12.0 | 16.0 | 17  | 32.0 | 36.0 |
| 8   | 14.0 | 18.0 | 18  | 34.0 | 38.0 |
| 9   | 16.0 | 20.0 | 19  | 36.0 | 40.0 |
| 10  | 18.0 | 22.0 | 20  | 38.0 | 42.0 |
| 11  | 20.0 | 24.0 |     |      |      |

深圳市连盛精密连接器有限公司

OPERATION

DRAW

SCALE

FIT

X.X

±0.30

UNIT

mm

X.XX

±0.20

CHECK

X.XXX

±0.10

APPROVE

Angle

±3°

SHEET

1/1

DIM

TOL

PROJ.

◆

PART NO.

1130300203

TITLE:

HY-NA

1 2 3 4 5 6 7 8 9