



产品承认书

SPECIFICATION FOR APPROVAL

客户名称:

CUSTOMER

我司料号:

OUR PART NO.

XR1050-820M

我司品名:

OUR PART NAME

MOLDING POWER INDUCTORS

送样日期:

DATE SAMPLES

数量:

QUANTITY

制造确认 MANUFACTURER APPROVE

拟制 DRAWN	审核 CHECKED	确认 APPROVED
Hufangting	RaoPing	ZhongCuilan

客户确认 CUSTOMER APPROVE

客户名称 CUSTOMER NAME:

客户料号 CUSTOMER P/N:

规格型号 DESCRIPTION:

XR1050 82uH $\pm 20\%$ 3.5A

检查结果: ☐ 合格 ☐ 不合格

签名及盖章:

INSPECT RESULT ACCEPT REJECT

SIGNATURE AND STAMP

说明 REMARK:

如对本承认书内容有异议请提出或标记发送至我司, 本承认书在未收到异议回复时于本承认书提供一周后生效。

If you have any objection to the contents of this acknowledgment, please raise it or send the mark to us. The acknowledgment will become effective one week after the acknowledgment is provided in the absence of any objection.

东莞市祥如电子有限公司

DONGGUAN XIANGRU ELECTRONICS CO., LTD

Tel: 0769-86346548 Fax: 0769-86346358

Email: dgxiangru@126.com

产品承认书


SPECIFICATION FOR APPROVAL

客户名称 CUSTOMER		日期 DATE	2024/06/21
客户物料编号 CUSTOMER P/N		客户规格型号 DESCRIPTION	XR1050 82uH $\pm 20\%$ 3.5A
我司物料编号 OUR PART NO	XR1050-820M	我司品名 OUR PART NAME	MOLDING POWER INDUCTORS

外观尺寸 Appearance of size


单位 Unit: mm

Recommended pad size推荐焊盘尺寸:



A	B	C	D	E	G	H	I	lettering
11.5MAX	10.1 ± 0.3	3.0 ± 0.3	5.0MAX	2.0 ± 0.3	2.9	11.2	3.5	820

• Reel and Taping Dimensions (UNIT:mm)



Type	W	A0	B0	D	E	F	K0	P0	P2	P	T	
	± 0.3	± 0.1	± 0.1	± 0.1	± 0.1	± 0.1	± 0.1	± 0.1	± 0.1	± 0.1	± 0.05	
XR1050	24.00	12.00	13.00	1.50	1.75	###	5.60	4.00	2.00	16.00	0.40	



产品承认书


SPECIFICATION FOR APPROVAL

客户名称 CUSTOMER		日期 DATE	2024/06/21
客户物料编号 CUSTOMER P/N		客户规格型号 DESCRIPTION	XR1050 82uH $\pm 20\%$ 3.5A
我司物料编号 OUR PART NO	XR1050-820M	我司品名 OUR PART NAME	MOLDING POWER INDUCTORS

Electrical characteristics 电气特性:

Part Number 型号	Inductance (uH) 电感量	精度 ($\pm$)	测定频率 Test Frequency (Hz/v)	直流阻抗 DC Resistance (m Ω) max.	饱和电流 Isat (A) Max. $\Delta L/L \cong -30\%$	温升电流 Irms (A) Max. $\Delta T \leq 40^{\circ}\text{C}$
XR1050-820M	82.0	20%	100 kHz, 1V	265.00	3.5	2.3

回流焊曲线 Reflow soldering profile:



Notes 注意事项:

- All test data is referenced to 25 C ambient所有测试数据均参考25° C环境温度.
- Operating temperature range -55°C to + 125°C工作温度范围-55°C至+125°C.
- Irms (A):DC current (A) that will cause an approximate ΔT of 40 ° C(reference ambient temperature is 25° °C)
Irms(A):将导致大约40° C ΔT 的直流电流(A) (参考环境温度为25° C).
- Isat(A):DC current (A) that will cause L0 to drop approximately30% Isat(A):将导致L0下降约30%的直流电流(A).
- The part temperature (ambient + temp rise) should not exceed 125 ° C under worst case operating conditions.Circuit design, component placement, PWB trace size and thickness, airflow and other cooling provisions all affect the part temperature. Part temperature should be verified in the end application.
在最坏的操作条件下, 零件温度(环境温度+温升)不应超过125° °C。电路设计、部件放置、PWB迹线尺寸和厚度、气流和其他冷却措施都会影响零件温度。应在最终应用中验证零件温度。

制表 MADE	审核 CHECKED	批准 APPROVED	
Hufangting	RaoPing	ZhongCuilan	