

BCM120S05D3

Silicon Carbide Schottky Diode

1200V, 5A

Description

BCM120S05D3 utilizes Bestirpower's advanced silicon carbide diode technology. This technology combines the benefits of excellent low forward voltage and robustness. Consequently, the family is suitable for application requiring high power efficiency


Applications

- Power factor correction(PFC)
- Solar inverter
- Uninterruptible power supply
- Motor drives
- Photo-voltaic inverter
- Electric car and charger

Features

V_{RRM}	I_F	$T_{J,max}$	Q_C
1200 V	5 A	175 °C	27nC

- Positive temperature coefficient
- Temperature-independent switching
- Maximum working temperature at 175 °C
- Unipolar devices and zero reverse recovery current
- Zero forward recovery current
- Essentially no switching losses
- Reduction of heat sink requirements
- High-frequency operation
- Reduction of EMI



Absolute Maximum Ratings (T_C = 25°C unless otherwise noted)

Symbol	Parameter	Value	Unit
V_{RRM}	Repetitive Peak Reverse Voltage	1200	V
I_F	Forward Current	$T_C = 25^{\circ}C$	13 A
		$T_C = 137^{\circ}C$	7 A
		$T_C = 148^{\circ}C$	5 A
$I_{F,SM}$	Non-Repetitive Forward Surge Current	$T_C = 25^{\circ}C, t_p = 10\text{ ms}$	40 A
		$T_C = 110^{\circ}C, t_p = 10\text{ ms}$	34 A
I^2dt value	$\int I^2 dt$	$T_C = 25^{\circ}C, t_p = 10\text{ ms}$	12.5 A ² s
P_{tot}	Power Dissipation	$T_C = 25^{\circ}C$	58 W
		$T_C = 110^{\circ}C$	25 W
T_J, T_{STG}	Operating Junction and Storage Temperature	-55 to +175	°C



Thermal Characteristics

Symbol	Parameter	Value	Unit
$R_{\theta C}$	Thermal Resistance, Junction to Case, Typ.	2.6	$^{\circ}\text{C}/\text{W}$

Electrical Characteristics ($T_C = 25^{\circ}\text{C}$ unless otherwise noted)

Symbol	Parameter	Test Conditions	Min	Typ	Max	Unit
V_{DC}	DC blocking voltage		1200	-	-	V
V_F	Forward Voltage	$I_F = 5\text{A}$, $T_C = 25^{\circ}\text{C}$	-	1.37	1.8	V
		$I_F = 5\text{A}$, $T_C = 175^{\circ}\text{C}$	-	1.8	-	
I_R	Reverse Current	$V_R = 1200\text{V}$, $T_C = 25^{\circ}\text{C}$	-	0.5	16	μA
		$V_R = 1200\text{V}$, $T_C = 175^{\circ}\text{C}$	-	8	-	
Q_C	Total Capacitive Charge	$V_R = 800\text{V}$, $T_j = 25^{\circ}\text{C}$, $Q_C = \int_0 V_{RC}(V) dV$	-	27	-	nC
C	Total capacitance	$V_R = 0\text{V}$, $f = 1\text{MHz}$	-	377	-	pF
		$V_R = 400\text{V}$, $f = 1\text{MHz}$	-	25	-	
		$V_R = 800\text{V}$, $f = 1\text{MHz}$	-	19	-	
E_C	Capacitance Stored Energy	$V_R = 800\text{V}$	-	6.8	-	μJ

Typical Performance Characteristics



Typical Performance Characteristics

Figure 3. Capacitance vs. Reverse Voltage




Figure 4. Total Capacitance Charge vs. Reverse Voltage




Figure 5. Capacitance Stored Energy




Figure 6. Power Derating




Figure 7. Current Derating






Figure 8. Transient Thermal Impedance



Package Outlines

TO252NC



COMMON DIMENSIONS

SYMBOL	mm		
	MIN	NOM	MAX
A	2.20	2.30	2.38
A1	0.00	-	0.12
A2	0.97	1.07	1.17
b	0.68	0.78	0.90
b3	5.20	5.33	5.46
c	0.43	0.53	0.61
D	5.98	6.10	6.22
D1	5.30REF		
E	6.40	6.60	6.73
E1	4.63	-	-
e	2.286BSC		
H	9.40	10.10	10.50
L	1.38	1.50	1.75
L1	2.90REF		
L2	0.51BSC		
L3	0.88	-	1.28
L4	0.50	-	1.00
L5	1.65	1.80	1.95
θ	0°	-	8°

* Dimensions in millimeters

Package Marking and Ordering Information

Part Number	Top Marking	Package	Packing Method	Reel Size	Tape Width	Quantity
BCM120S05D3	BCM120S05D3	TO252NC	Tape & Reel	330 mm	16 mm	2500 units

Disclaimer

Bestirpower reserve the right to make changes, corrections, enhancements, modifications, and improvements to Bestirpower products and/or to this document at any time without notice.

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. Bestirpower does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Products or technical information described in this document.

This document is the property of Bestirpower Co., LTD., and not allowed to copy or transformed to other format if not under the authority approval.

© 2023 Bestirpower – All rights reserved