

1. Product Information

1.1 Features

- ☒ Advanced trench cell design
- ☒ Low Thermal Resistance

1.2 Applications

- ☒ Motor drivers
- ☒ DC - DC Converter


1.3 Quick reference

- ☒ $BV \geq 150\text{ V}$
- ☒ $P_{tot} \leq 312\text{ W}$
- ☒ $I_D \leq 155\text{ A}$
- ☒ $R_{DS(ON)} \leq 5.5\text{ m}\Omega @ V_{GS} = 10\text{ V}$
- ☒ $R_{DS(ON)} \leq 7.0\text{ m}\Omega @ V_{GS} = 6\text{ V}$

2. Pin Description


Pin	Description
1	Gate (G)
2	Drain (D)
3	Source (S)

Simplified Outline



Top View
TO-220C-3L

Symbol



3. Limiting Values


Symbol	Parameter	Conditions	Min	Max	Unit
V _{DS}	Drain-Source Voltage	T _C = 25 °C	-	150	V
V _{GS}	Gate-Source Voltage	T _C = 25 °C	-	±20	V
I _D ^{*,***}	Drain Current (DC)	T _C = 25 °C, V _{GS} = 10 V	-	155	A
		T _C = 100 °C, V _{GS} = 10 V	-	98	A
I _{DM} [*]	Drain Current (Pulsed)	T _C = 25 °C, V _{GS} = 10 V	-	380	A
P _{tot}	Drain power dissipation	T _C = 25 °C	-	312	W
T _{stg}	Storage Temperature		-55	150	°C
T _J	Junction Temperature		-	150	°C
I _S	Continuous-Source Current	T _C = 25 °C	-	155	A
E _{AS}	Single Pulsed Avalanche Energy	V _{DD} =50V , L=1.0mH	-	1250	mJ
R _{θJA} ^{**}	Thermal Resistance- Junction to Ambient		-	42	°C/W
R _{θJC} ^{**}	Thermal Resistance- Junction to Case		-	0.4	

Notes :

- * Pulse width ≤ 300 μs, duty cycle ≤ 2 %
- ** Surface Mounted on 1 in² pad area, t ≤ 10 sec
- *** Limited by bonding wire

4. Marking Information

Product Name	Marking
WTM0550N15JP	WPM 0550N15JP XXX YYWW



5. Ordering Code

Product Name	Package	Quantity
WTM0550N15JP	TO220C	50

6. Electrical Characteristics (T_A = 25 °C Unless Otherwise Noted)

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
Static Characteristics						
BV _{DSS}	Drain-Source Breakdown Voltage	V _{GS} = 0 V, I _{DS} = 250 μA	150	-	-	V
V _{GS(th)}	Gate Threshold Voltage	V _{DS} = V _{GS} , I _{DS} = 250 μA	2	-	4	V
I _{DSS}	Drain Leakage Current	V _{DS} = 120 V, V _{GS} = 0 V	-	-	1	μA
I _{GSS}	Gate Leakage Current	V _{GS} = 0 V, V _{GS} = ± 20 V	-	-	±100	nA
R _{DS(ON)} ^a	On-State Resistance	V _{GS} = 10 V, I _{DS} = 30 A	-	4.8	5.5	m Ω
		V _{GS} = 6 V, I _{DS} = 20 A	-	5.8	7.0	
Diode Characteristics						
V _{SD} ^a	Diode Forward Voltage	I _{SD} = 30 A, V _{GS} = 0 V	-	-	1.3	V
t _{rr}	Reverse Recovery Time	I _{DS} = 30 A, V _{GS} = 0 V dI _{SD} /dt = 100 A/μs	-	111	-	nS
Q _{rr}	Reverse Recovery Charge		-	381	-	nC
Dynamic Characteristics ^b						
C _{iss}	Input Capacitance	V _{GS} = 0 V, V _{DS} = 75 V Frequency = 1 MHz	-	8218	-	pF
C _{oss}	Output Capacitance		-	572	-	
C _{rss}	Reverse Transfer Capacitance		-	23	-	
t _{d(on)}	Turn-on Delay Time	V _{DS} = 75 V, V _{GEN} = 10 V, R _G = 3.9 Ω, R _L = 2.4 Ω, I _{DS} = 30 A	-	17	-	nS
t _r	Turn-on Rise Time		-	55	-	
t _{d(off)}	Turn-off Delay Time		-	57	-	
t _f	Turn-off Fall Time		-	57	-	
Gate Charge Characteristics ^b						
Q _g	Total Gate Charge	V _{DS} = 75 V, V _{GS} = 10 V, I _{DS} = 30 A	-	111	-	nC
Q _{gs}	Gate-Source Charge		-	43	-	
Q _{gd}	Gate-Drain Charge		-	14	-	


Notes :

a : Pulse test ; pulse width ≤ 300 μs, duty cycle ≤ 2%


b : Guaranteed by design, not subject to production testing

7. Typical Characteristics


Power Capability




Current Capability



Safe Operating Area




Transient Thermal Impedance




7. Typical Characteristics (cont.)


Output Characteristics




On Resistance







Transfer Characteristics



Normalized Threshold Voltage




7. Typical Characteristics (cont.)



8. Package Dimensions

TO-220C-3L



Symbol	Dimensions In Millimeters	
	MIN.	MAX.
A	9.80	10.20
A1	7.80	8.20
A2	4.80	5.20
B	13.00	13.40
C	4.35	4.65
C1	1.15	1.45
D	0.65	0.95
E	3.45	3.75
F	2.85	3.15
G	6.40	6.80
H	0.35	0.65
J	28.68	29.08
K	2.80	3.20
M	1.15	1.45
N	TYP2.54	
P	2.20	2.60
Q	9.00	9.40
S	0.15	0.35
T	0.15	0.35
U	2.65	2.95
DIA	2.5±0.1 MAX0.5	

WPMtek reserves the right to make changes to the product specification and data in this document without notice. WPMtek makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does WPMtek assume any liability arising from the application or use of any products or circuits, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Any enquiry, please write to sales@wpmtek.com for further information.