

General Features


- Advanced Planar Process
- $R_{DS(ON),typ.}=85m\Omega@V_{GS}=10V$
- Low Gate Charge Minimize Switching Loss
- Rugged Poly silicon Gate Structure

Applications

- BLDC Motor Driver
- Electric Welder
- High Efficiency SMPS

Product Description

BV_{DSS}	500	V
I_D	40	A
$R_{DS(ON),Typ.}$	85	m Ω



Device	Package	Marking
WTM40N50VMP	TO-247	WPM 40N50VMP XXX YYWW

Absolute Maximum Ratings $T_j=25^{\circ}C$

Symbol	Parameter	XTMF50N40P	Unit
V_{DSS}	Drain-to-Source Voltage	500	V
V_{GSS}	Gate-to-Source Voltage	± 30	
I_D	Continuous Drain Current	40	A
I_{DM}	Pulsed Drain Current at $V_{GS}=10V$	180	
E_{AS}	Single Pulse Avalanche Energy	5000	mJ
P_D	Power Dissipation	540	W
	Derating Factor above $25^{\circ}C$	4.32	W/ $^{\circ}C$
T_L	Soldering Temperature Distance of 1.6mm from case for 10 seconds	300	$^{\circ}C$
$T_J \& T_{STG}$	Operating and Storage Temperature Range	-55 to 150	

Caution: Stresses greater than those listed in the “Absolute Maximum Ratings” may cause permanent damage to the device.

Thermal Characteristics

Symbol	Parameter	WTM40N50VMP	Unit
$R_{\theta JC}$	Thermal Resistance, Junction-to-Case	0.23	$^{\circ}\text{C/W}$
$R_{\theta JA}$	Thermal Resistance, Junction-to-Ambient	50	$^{\circ}\text{C/W}$

Electrical Characteristics $T_j=25^{\circ}\text{C}$

OFF Characteristics

Symbol	Parameter	Min	Typ	Max	Unit	Test Condition
BV_{DSS}	Drain-to-Source Breakdown Voltage	500	--	--	V	$V_{GS}=0V, I_D=250\mu A$
I_{DSS}	Drain-to-Source Leakage Current	--	--	5	μA	$V_{DS}=500V, V_{GS}=0V$
		--	--	500		$V_{DS}=400V, V_{GS}=0V, T_J=125^{\circ}\text{C}$
I_{GSS}	Gate-to-Source Leakage Current	--	--	+100	nA	$V_{GS}=+30V, V_{DS}=0V$
		--	--	-100		$V_{GS}=-30V, V_{DS}=0V$

ON Characteristics

Symbol	Parameter	Min	Typ	Max	Unit	Test Condition
$R_{DS(ON)}$	Static Drain-to-Source On-Resistance ^[4]	--	85	100	$m\Omega$	$V_{GS}=10V, I_D=23A$
$V_{GS(TH)}$	Gate Threshold Voltage	2.0	--	4.0	V	$V_{DS}=V_{GS}, I_D=250\mu A$
gfs	Forward Transconductance ^[4]	--	32	--	S	$V_{DS}=25V, I_D=23A$

Dynamic Characteristics

Symbol	Parameter	Min	Typ	Max	Unit	Test Condition
C_{iss}	Input Capacitance	--	6.8	--	nF	$V_{GS}=0V$, $V_{DS}=25V$, $f=1.0MHz$
C_{rss}	Reverse Transfer Capacitance	--	0.1	--		
C_{oss}	Output Capacitance	--	0.7	--		
Q_g	Total Gate Charge	--	138	--	nC	$V_{DD}=250V$, $I_D=20A$, $V_{GS}=0$ to $10V$
Q_{gs}	Gate-to-Source Charge	--	38	--		
Q_{gd}	Gate-to-Drain (Miller) Charge	--	27	--		

Resistive Switching Characteristics

Symbol	Parameter	Min	Typ	Max	Unit	Test Condition
$t_{d(ON)}$	Turn-on Delay Time	--	25	--	ns	$V_{DD}=250V$, $I_D=20A$, $V_{GS}=10V$ $R_G=10\Omega$
t_{rise}	Rise Time	--	39	--		
$t_{d(OFF)}$	Turn-Off Delay Time	--	100	--		
t_{fall}	Fall Time	--	36	--		

Source-Drain Body Diode Characteristics

Symbol	Parameter	Min	Typ	Max	Unit	Test Condition
I_{SD}	Continuous Source Current ^[4]	--	--	46	A	Integral pn-diode in MOSFET
I_{SM}	Pulsed Source Current ^[4]	--	--	180		
V_{SD}	Diode Forward Voltage	--	--	1.5	V	$I_S=40A$, $V_{GS}=0V$
t_{rr}	Reverse recovery time	--	730	--	ns	$V_{GS}=0V$, $I_F=40A$, $di_F/dt=100A/\mu s$
Q_{rr}	Reverse recovery charge	--	3.0	--	uC	

[1] Pulse width $\leq 380\mu s$; duty cycle $\leq 2\%$

Typical Characteristics

Figure 1. Maximum Transient Thermal Impedance




Figure 2 . Max. Power Dissipation vs Case Temperature




Figure 3. Maximum Continuous Drain Current vs Tc




Figure 4. Typical Output Characteristics





Figure5. Typical Drain-to-Source ON Resistance vs Gate Voltage and Drain Current



Typical Characteristics(Cont.)

Figure 6. Peak Current Capability




Figure 7. Typical Transfer Characteristics




Figure 8. Unclamped Inductive Switching Capability




Figure 9. Typical Drain-to-Source ON Resistance vs Drain Current





Figure 10. Typical Drain-to-Source ON Resistance vs Junction Temperature



Typical Characteristics(Cont.)

Figure 11. Typical Breakdown Voltage vs Junction Temperature




Figure 12. Typical Threshold Voltage vs Junction Temperature




Figure 13. Maximum Forward Bias Safe Operating Area




Figure 14. Typical Capacitance vs Drain-to-Source Voltage




Figure 15. Typical Gate Charge vs Gate-to-Source Voltage





Figure 16. Typical Body Diode Transfer Characteristics



Test Circuits and Waveforms (cont.)




Fig. 2.1 Switching Test Circuit




Fig. 2.2 Switching Waveforms




Fig. 3.1 Gate Charge Test Circuit




Fig. 3.2 Gate Charge Waveform




Fig. 4.1 Unclamped Inductive Switching Test Circuit




Fig. 4.2 Unclamped Inductive Switching Waveforms

WPMtek reserves the right to make changes to the product specification and data in this document without notice. WPMtek makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does WPMtek assume any liability arising from the application or use of any products or circuits, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Any enquiry, please write to sales@wpmtek.com for further information.