

Differential Probe PT-5240



Characteristic

- 2% accuracy.
- Adaptor power supply.
- Standard BNC interface, compatible with any brand's oscilloscope.

Model	PT-5240
Bandwidth(-3dB)	500X:DC-75MHz; 5000X:DC-20MHz
Attenuation Ratio	500X, 5000X
Accuracy	±2%
Input differential Vp-p	500X:4kV; 5000X:40kV
Input differential V AC RMS	14kV
Input differential V DC	500X:2kV; 5000X:20kV
Common mode voltage RMS	7kV
Rise Time	≥4.7ns
Input Impedance	55MΩ//2pF(Single-ended to ground); 110MΩ//1pF(Between the two ends)
Noise RMS	≤1mV
CMRR(Typical)	60Hz:>80dB; 100Hz:>60dB; 1MHz:>50dB
Oscilloscope input impedance	1MΩ
Power adaptor	9V DC
Temperature	0~50°C
Humidity	10~85% RH
Weight	390g
Dimension(L*W*H)	218x83x30mm

● ACCESSORIES



9V Adapter



BP-250



BP-266N



BP-276N



BP-366A

GUANGZHOU PINTECH CO.,LTD

Web:www.pintech.com.cn

Tel:020-82510899

E-mail:sales@pintech.com.cn

Main Products

Optical Isolated Voltage Probe, Differential probe, Oscilloscope probe, High voltage probe, High frequency current probe, Current probe, Digital high voltage meter, High voltage amplifier, Power amplifier, ESD generator, Function generator, Oscilloscope, Spectrum analyzer, multimeter, High voltage power supply, AC power supply, DC power supply and Power equipment instrument.