






X	
PART NO	vigor
2	G2
3	G3
4	G4
5	G5
6	G6
7	G7
8	G8



Specification:
 1.Rating: DC 30V 50mA
 2.Travel: 2.5±0.1mm
 3.Operating Force:A-B 250gf±100gf
 B-A 250gf±100gf
 4.Contact Resistance:100mΩ Max
 5.Life:10,000 Cycles Min



4	TERMINAL	BRASS STRIP
3	TERMINAL BASE	PHENOLIC RESIN
2	FRAME	STEEL STRIP
1	KNOB	POM
NO.	PART NAME	MATERIAL

[illegible]